

**SENCITY® OCCHIO PLUS**

1399.32.0020

**Properties**

- Omnidirectional antenna for Cellular bands from 617 MHz till 6000 MHz
- Gain of 4 dBi with Vertical polarisation
- PIM better than -153 dBc at 2x43 dBm
- Supports MIMO 4x4 in Cellular and Wi-Fi Bands
- Nex10 female connector
- Smart bracket system is included



<b>Electrical data</b>				
	<b>Band 1</b>	<b>Band 2</b>	<b>Band 3</b>	<b>Band 4</b>
Frequency	617 MHz ... 960 MHz	1427 MHz ... 1660 MHz	1695 MHz ... 2690 MHz	3300 MHz ... 4200 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2	1.8	1.7	1.7
Gain	3 dBi	4 dBi	4 dBi	4 dBi
Isolation between Ports	15 dB	18 dB	20 dB	25 dB
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	63 W	48 W	34 W	23 W

	<b>Band 5</b>
Frequency	4500 MHz ... 6000 MHz
Impedance	50 Ω
VSWR	1.7
Gain	5 dBi
Isolation between Ports	25 dB
Ambient Temperature	25 °C
Composite Power max	16 W

**Electrical remarks**

IMD level	-153 dBc at carrier power 2x 43 dBm
-----------	-------------------------------------

**Ports**

	<b>Port 1</b>	<b>Port 2</b>	<b>Port 3</b>	<b>Port 4</b>
Connector	NEX10, jack (female)	NEX10, jack (female)	NEX10, jack (female)	NEX10, jack (female)

**SENCITY® OCCHIO PLUS**

1399.32.0020

<b>Ports</b>				
	<b>Port 1</b>	<b>Port 2</b>	<b>Port 3</b>	<b>Port 4</b>
Polarization	vertical	vertical	vertical	vertical

<b>Connections</b>				
	Port 1	Port 2	Port 3	Port 4
Band 1	✓	✓	✓	✓
Band 2	✓	✓	✓	✓
Band 3	✓	✓	✓	✓
Band 4	✓	✓	✓	✓
Band 5	✓	✓	✓	✓

<b>Mechanical data</b>	
Weight	0.89 kg
Dimensions	45 mm x 275 mm (Height x Diameter)

<b>Material data</b>	
Radome material	PC (Polycarbonate)
Radome colour	White
Back plate/base plate plating	Black

<b>Environmental data</b>	
Operation temperature	0 °C ... 55 °C
Storage temperature	-40 °C ... 85 °C
Environment (application)	Indoor
Flammability rating	UL 94-V0

<b>Ordering information</b>		
Item description	Item number	Product name
1399.32.0020	85189602	SENCITY® OCCHIO PLUS

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P35385 / Date of publication: 08.08.2025 / uncontrolled copy