


COAXIAL CONNECTOR, N, 50 Ohm, Right angle cable plug (male)

16_N-50-9-6/033_-

Properties

- Field mountable connector series Quick-fit
- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL



Product configuration		
Interface type	Gender	Standard
N	plug	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data		
Piece parts	Material	Plating
Centre contact	Bronze / Brass	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE / PPE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 2.5 GHz	30 dB	1.065
2.5 GHz ... 3 GHz	26 dB	1.1

Mechanical data	
Weight	0.164 kg
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	clamped

COAXIAL CONNECTOR, N, 50 Ohm, Right angle cable plug (male)

16_N-50-9-6/033_-

Environmental data	
Operation temperature	-40 °C ... 85 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23007299	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
23007299	16_N-50-9-6/033_-E	Single

Suitable cables	
Cable group	M9 - 9 mm / 50 Ohm
Suitable cables	SUCOFEEED_1/2_HF_FR
	SUCOFEEED_1/2_HF

Additional Information	
Remarks	Stripping tool: 23001006 74_Z-0-9-12
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
23001006	74_Z-0-9-15	Cable stripping tool

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3068 / Date of publication: 11.07.2025 / uncontrolled copy