

Control station, Harmony, plastic, yellow, 1 red mushroom head push button 40mm, emergency stop turn to release 1NO + 2NC, unmarked, UL CSA certified

XALK178GH7

### Main

Range of product	Harmony XALK	
Product or component type	Complete control station	
Device short name	XALK	
Product destination	For XB5 Ø 22 mm control and signalling units	
Control station application	Emergency stop function Emergency switching off function	
Colour of base of enclosure	Light grey (RAL 7035)	
Colour of cover	Yellow (RAL 1021)	
Material	Polycarbonate	
Operator profile	1 mushroom head push-button	
Operators description	Red unmarked 1 NO + 2 NC	
Reset	Turn to release	
Control station composition	1 mushroom head Ø 40 mm push-button, red 1 NO + 2 NC unmarked marking	
Contact operation	Slow-break	

# Complementary

Cable entry	1 knock-out for cable entry 014 mm 2 knock-outs for Pg 13 cable gland and ISO M20 012 mm
Product weight	0.194 kg
Resistance to high pressure washer	7000000 Pa at 55 °C, distance : 0.1 m
Positive opening	With conforming to IEC 60947-5-1 appendix K
Operating travel	1.5 mm (NC changing electrical state) 2.6 mm (NO changing electrical state) 4.3 mm (total travel)
Operating force	44 N NC + NO changing electrical state
Mechanical durability	300000 cycles
Connections - terminals	Screw clamp terminals, <= 2 x 1.5 mm² with cable end conforming to IEC 60947-1 Screw clamp terminals, >= 1 x 0.22 mm² without cable end conforming to IEC 60947-1
Tightening torque	0.81.2 N.m conforming to IEC 60947-1
Shape of screw head	Cross compatible with Philips no 1 screwdriver Cross compatible with pozidriv No 1 screwdriver Slotted compatible with flat Ø 4 mm screwdriver Slotted compatible with flat Ø 5.5 mm screwdriver
Contacts material	Silver alloy (Ag/Ni)

Short-circuit protection	10 A cartridge fuse type gG conforming to IEC 60947-5-1	
[Ith] conventional free air thermal current	10 A conforming to IEC 60947-5-1	
[Ui] rated insulation voltage	600 V (pollution degree 3) conforming to IEC 60947-1	
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-1	
[le] rated operational current	3 A at 240 V, AC-15, A600 conforming to IEC 60947-5-1 6 A at 120 V, AC-15, A600 conforming to IEC 60947-5-1 0.1 A at 600 V, DC-13, Q600 conforming to IEC 60947-5-1 0.27 A at 250 V, DC-13, Q600 conforming to IEC 60947-5-1 0.55 A at 125 V, DC-13, Q600 conforming to IEC 60947-5-1 1.2 A at 600 V, AC-15, A600 conforming to IEC 60947-5-1	
Electrical durability	1000000 cycles, AC-15, 2 A at 230 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 3 A at 120 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 4 A at 24 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.2 A at 110 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.5 A at 24 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C	
Electrical reliability	Λ < 10exp(-6) at 5 V, 1 mA conforming to IEC 60947-5-4 Λ < 10exp(-8) at 17 V, 5 mA conforming to IEC 60947-5-4	

# **Environment**

Protective treatment	тн
Ambient air temperature for storage	-4070 °C
Ambient air temperature for operation	-4070 °C
Overvoltage category	Class II conforming to IEC 60536
IP degree of protection	IP66 conforming to IEC 60529 IP67 IP69 IP69K
NEMA degree of protection	NEMA 13 NEMA 4X
IK degree of protection	IK03 conforming to IEC 62262
Standards	IEC 60364-5-53 IEC 60947-5-4 IEC 60947-5-5 IEC 60947-5-1 CSA C22.2 No 14 ISO 13850 JIS C 4520 IEC 60947-1 UL 508 IEC 60204-1
Product certifications	CSA UL listed
Vibration resistance	5 gn (f= 12500 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	7.200 cm
Package 1 Width	7.200 cm
Package 1 Length	9.900 cm
Package 1 Weight	180.000 g



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Total lifecycle Carbon footprint	2
Environmental Disclosure	Product Environmental Profile

### **Use Better**

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration


#### **Use Again**

○ Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

# XALK178GH7

## **Dimensions Drawings**

### **Dimensions**



(1) 2 knock-outs for Pg 13.5 cable gland, maximum capacity 12 mm/0.47 in. (2) Knock-out for cable entry, maximum capacity 14 mm/0.55 in.

Control station fitted with:	c in mm	c in in.
Flush pushbutton	62	2.44
Pilot light	64	2.52
Illuminated pushbutton	65.5	2.58
Projecting pushbutton	66	2.60
Selector switch	80	3.15
Mushroom head pushbutton	91.5	3.58
Latching mushroom head Emergency stop pushbutton with key	115	4.53
Key switch	105.5	4.15

### **Technical Illustration**

#### **Dimensions**




Image of product / Alternate images

## **Alternative**











