

COAXIAL CONNECTOR, SMA, 50 Ohm, Right angle cable plug (male)

16_SMA-50-3-146/133_N

Properties

- Excellent return loss
- Intermateable with PC3.5 and SK
- Applicable in frequencies up to 18 GHz

**Product configuration**

Interface type	Gender	Standard
SMA	plug	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data

Weight	0.0057 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	crimped

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, SMA, 50 Ohm, Right angle cable plug (male)

16_SMA-50-3-146/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22649909	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
22651733	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22649909	16_SMA-50-3-146/133_NE	Single
22651733	16_SMA-50-3-146/133_NH	Bulk 100 pcs

Suitable cables	
Cable group	U9 - 3 mm / 50 Ohm
	U41 - 3 mm / 50 Ohm
	U11 - 3 mm / 50 Ohm
Suitable cables	RG_223_/U
	RG_142_B/U
	ENVIROFLEX_142
Additional cables	RG_400_/U
	RADOX_RF_142

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543124	74_Z-0-0-14	Locator

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3022 / Date of publication: 11.07.2025 / uncontrolled copy