

servo motor SH3 100 5,8Nm,key,single,nobrake, 90°conn.IP65/IP65,6k RPM

SH31002P11A2100

Main

Range compatibility	PacDrive 3
Device short name	SH3
Product or component type	Servo motor

Complementary

Complementary		
Maximum mechanical speed	6000 rpm	
[Us] rated supply voltage	115480 V	
Network number of phases	Three phase	
Continuous stall current	4.8 A	
Continuous stall torque	5.8 N.m at 115480 V three phase	
Continuous power	1900 W	
Peak stall torque	18.3 N.m at 115480 V three phase	
Nominal output power	580 W at 115 V single phase 1090 W at 230 V single phase 1930 W at 400 V three phase 2210 W at 480 V three phase	
Nominal torque	5.5 N.m at 115 V single phase 5.2 N.m at 230 V single phase 4.6 N.m at 400 V three phase 4.4 N.m at 480 V three phase	
Nominal speed	1000 rpm at 115 V single phase 2000 rpm at 230 V single phase 4000 rpm at 400 V three phase 4800 rpm at 480 V three phase	
Maximum current Irms	17.1 A	
Shaft end	Parallel key	
Shaft diameter	19 mm	
Shaft length	40 mm	
key width	6 mm	
IP degree of protection	IP65 motor: conforming to IEC 60034-5 IP65 shaft bushing: conforming to IEC 60034-5	
Encoder type	Absolute single turn SinCos Hiperface	
Speed feedback resolution	128 periods	
Holding brake	Without	
Mounting support	International standard flange	
Motor flange size	100 mm	

Electrical connection	Rotatable right angled connector	
Torque constant	1.21 N.m/A at 120 °C	
Back emf constant	77 V/krpm at 20 °C	
Number of motor poles	4.0	
Rotor inertia	2.31 kg.cm²	
Stator resistance	2.4 Ohm	
Stator inductance	6.75 mH	
Maximum radial force Fr	990 N at 1000 rpm 790 N at 2000 rpm 690 N at 3000 rpm 620 N at 4000 rpm	
Maximum axial force Fa	160 N	
Type of cooling	Natural convection	
Length	204.5 mm	
Centring collar diameter	95 mm	
Centring collar depth	3.5 mm	
Number of mounting holes	4	
Mounting holes diameter	9.0 mm	
Circle diameter of the mounting holes	115 mm	
Product weight	5.8 kg	
Sizing reference	SH31002P	
Network number of phases	3	
Temperature copper hot	130 °C	
compatible drive output current 3s peak 2	15 A	
Electrical connection	rotatable right angled connector	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19.700 cm
Package 1 Width	22.300 cm
Package 1 Length	40.700 cm
Package 1 Weight	6.764 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Total lifecycle Carbon footprint	4560
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ead0850d-370a-47c5-8cf7-1d93c2c974a4
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Again

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No