

COAXIAL CONNECTOR, SMB, 50 Ohm, Right angle cable plug (male)

16_SMB-50-2-51/111_N

Properties

- Snap-on mechanism provides a fast and reliable connection
- Ideal for applications with high packaging density
- Applicable in frequencies up to 4 GHz

**Product configuration**

Interface type	Gender	Standard
SMB	plug	IEC 60169-10_MIL-STD-348A/311_CECC 22130

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Electrical data

Impedance	50 Ω
Interface frequency	4 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 4 GHz	22 dB	1.17

Mechanical data

Weight	0.0038 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	crimped

COAXIAL CONNECTOR, SMB, 50 Ohm, Right angle cable plug (male)

16_SMB-50-2-51/111_N

Engagement / Disengagement force		
	Engagement	Disengagement
Interface force min	8 N	8 N
Interface force max	63 N	63 N

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22648058	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
22658985	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22648058	16_SMB-50-2-51/111_NE	Single
22658985	16_SMB-50-2-51/111_NH	Bulk 100 pcs

Suitable cables	
Cable group	U4 - 2 mm / 50 Ohm
Suitable cables	K_02252_D
	G_02232_D
	ENVIROFLEX_316_D

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22644541	74_Z-0-0-177	Assembly tool

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2995 / Date of publication: 11.07.2025 / uncontrolled copy