



Timing Relay, Type JCK, plug In, on delay, programmable, 0.5 second to 999 hours, 10A, 240 VAC, 240 VAC 50/60 Hz

9050JCK60V24

Product availability: Stock - Normally stocked in distribution facility

## Main

product range	9050JCK
product type	Timer
timing mode	On-delay
timing range	0.199.9 h
	1999 h
	0.059.99 s
	1999 min
	1999 s
	0.199.9 s
supply voltage	240 V AC

# Complementary

power consumption	3.2 VA
current rating	10 A
switch function	DPDT
contact composition	2 NO + 2 NC
contact material	Silver nickel
maximum switching voltage	240 V AC
mounting type	Socket
number of pins	8
shape of pins	Tubular
for use with	8501NR52 8501NR51

## **Environment**

certifications	UL Recognized UL Listed CE
ambient temperature range - operational	-2850 °C (-18122 °F)
Height	2.4 in (60 mm)
Width	1.7 in (44 mm)
Depth	3.6 in (91 mm)

# Ordering and shipping details

Category US10CP221652

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0CP2
GTIN	785901136903
Returnability	Yes
Country of origin	US

# **Packing Units**

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	4.30 in (10.922 cm)
Package 1 Length	2.60 in (6.604 cm)
Package weight(Lbs)	4.480 oz (127.006 g)

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	50	

#### **Use Better**


Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

## **Use Again**

○ Repack and remanufacture		
Take-back	No	


# **Dimensions Drawings**

# **Approximate Dimensions**



## Connections and Schema

## **Connections and Wiring Diagrams**



(1) Do not apply DC voltage to the 240 Vac timers (voltage code V24).