


COAXIAL CONNECTOR, BNC, 75 Ohm, Straight cable jack (female)

21_BNC-75-2-5/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration		
Interface type	Gender	Standard
BNC	jack	Interface compatible with IEC 61169-8
Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating
Electrical data		
Impedance	75 Ω	
Interface frequency	1 GHz	
Mechanical data		
Weight	0.0131 kg	
Mating cycles	500	
Cable entry centre contact	crimped	
Cable entry outer contact	crimped	
Environmental data		
Operation temperature	-65 °C ... 165 °C	

COAXIAL CONNECTOR, BNC, 75 Ohm, Straight cable jack (female)

21_BNC-75-2-5/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22641780	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
22645904	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22641780	21_BNC-75-2-5/133_NE	Single
22645904	21_BNC-75-2-5/133_NH	Bulk 100 pcs

Suitable cables	
Cable group	U5 - 2 mm / 75 Ohm
Suitable cables	RG_187_A/U
	RG_179_B/U

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543181	76_Z-0-2-1	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2915 / Date of publication: 11.07.2025 / uncontrolled copy