

# Product data sheet

## Characteristics

# 26960

## voltage release - MN - 220..240 V AC



Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

Range of product	Multi 9
Product or component type	Undervoltage release
Device short name	MN
[Uc] control circuit voltage	220...240 V AC 50/60 Hz
Control type	Standard
9 mm pitches	2
Product compatibility	C120 DPN C60 C60CTRL N40 IDPN

### Complementary

Range compatibility	Acti 9: Acti 9 iDPN Multi 9: Multi 9 N40 Multi 9: Multi 9 C60
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	3.25 in (82.5 mm)
Width	0.71 in (18 mm)
Depth	2.68 in (68 mm)
Connections - terminals	Clamp terminal 1 cable(s) 0 in <sup>2</sup> (2.5 mm <sup>2</sup> ) flexible Clamp terminal 1 cable(s) 0 in <sup>2</sup> (2.5 mm <sup>2</sup> ) rigid Clamp terminal 2 cable(s) 0 in <sup>2</sup> (1.5 mm <sup>2</sup> ) flexible Clamp terminal 2 cable(s) 0 in <sup>2</sup> (1.5 mm <sup>2</sup> ) rigid
Wire stripping length	0.35 in (9 mm)
Tightening torque	8.85 lbf.in (1 N.m)

### Environment

Standards	EN/IEC 60947-5-1
Product certifications	LCIE KEMA ASEFA ASTA
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 131 °F (55 °C)
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

### Ordering and shipping details

Category	01078 - DE2 MISC
Discount Schedule	DE2
GTIN	00785901855965
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8000000000000000
Returnability	N
Country of origin	BE

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1216 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

## Contractual warranty

Warranty period	18 months
-----------------	-----------