



APC Back-UPS Pro, 1500VA/ 900W, Tower, 120V, 10x NEMA 5-15R outlets, AVR, USB Type A + C ports, LCD, User Replaceable Battery

BR1500MS2

Overview

Lead time	Usually in Stock
Main	
Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	900 W
rated power in VA	1500 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	6 NEMA 5-15R 4 NEMA 5-15R surge
Cable length	6 ft (1.8 m)
Number of cables	1
Battery Type	Lead-Acid battery
Range of Product	Back-UPS Pro

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	16 h
RBC Quantity	1
Battery Charge Power (Watts)	16 W rated
Battery design life	35 year(s)
Extendable Run Time	0
Replacement battery	APCRBC163 ☐

General

Provided equipment	Coaxial cable	
	User Manual	
	USB cable	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

product web sub-family	Gaming performance
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

color	Black aluminium
Height	10.24 in (26 cm)
Width	3.94 in (10 cm)
Depth	14.49 in (36.8 cm)
Net Weight	27.6 lb(US) (12.5 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

Input Frequency	60 Hz +/- 3 Hz
Plug standard	NEMA 5-15P
Efficiency at full load	88147 V
Maximum Input Current per Phase	12 Δ

Output

Max Configurable Power (Watts)	900 W
Output frequency	60 Hz +/- 3 Hz sync to mains
Topology	Line Interactive
Waveform Type	Sine wave
Maximum configurable power in VA	1500 VA
Transfer Time	8ms typical : 10 ms maximum

Conformance

Product Certifications	ENERGY STAR V2.0 (USA) NOM TUV C-US certified
Equipment protection policy	Lifetime : \$500000

Environmental

Ambient Air Temperature for Operation	32104 °F (040 °C)
Relative Humidity	095 % non-condensing
Operating altitude	03000 ft
Ambient Air Temperature for Storage	5104 °F (-1540 °C)
Storage Relative Humidity	095 % non-condensing

Storage altitude	05000 ft (01524 m)
Acoustic level	45 dBA

Communications & Management

control panel	Multi-function LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	1080 J
Filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: in
Data line protection	Coaxial cable for CATV/SATV/modem/audio-video

Ordering and shipping details

GTIN 731304426103

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	14.12 in (35.87 cm)	
Package 1 Width	18.98 in (48.2 cm)	
Package 1 Length	8.78 in (22.3 cm)	
Package 1 Weight	31.3 lb(US) (14.2 kg)	
SCC14	10731304426100	

Contractual warranty

Warranty 3 year repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes	
Packaging without single use plastic	No	
EU RoHS Directive	Compliant with Exemptions	
SCIP Number	50414655-abe7-48e2-9b8c-578e40cce4a8	
REACh Regulation	REACh Declaration	
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)	

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Product data sheet

BR1500MS2

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features



Image of product / Alternate images

Alternative



