

Socket, SE Relays general purpose relay accessory, 3PDT, 16A, 300 V, 11 pins, screw clamping terminal, 784 series

70-783D11-1A

Product availability: Stock - Normally stocked in distribution facility

Main

| Product Range | Legacy | |
|-----------------------|---|--|
| | Logacy | |
| Product Type | Socket | |
| Product Compatibility | relay 783XCX suppressor module 70-ASMM diode 70-ASMD signalling device 70-ASMLG suppressor module 70-ASMR | |
| Number of Terminals | 11 | |
| Switch Function | 3PDT | |
| Contact Composition | 3 NO + 3 NC | |

Complementary

| Rated Current | 16 A |
|--------------------------------|--|
| [Ue] rated operational voltage | 300 V |
| Contact Terminal Arrangement | Mixed |
| Connections Terminals | screw clamp terminals solid for output screw clamp terminals stranded for output |
| Fixing Mode | By screw M3.5, M3.5 panel Clip-on 35 mm symmetrical rail |
| Shape of Screw Head | Combination roundhead |
| Product Weight | 1.9 oz (55 g) |
| Width | 1.6 in (40 mm) |
| Depth | 2.2 in (57 mm) |

Environment

| Ambient Air Temperature for Storage | -40221 °F (-40105 °C) |
|--|-----------------------|
| Ambient Air Temperature for Operation | -40131 °F (-4055 °C) |
| IP Degree of Protection | IP20 |
| Flame Retardance | UL94-V0 |
| Product Certifications | UL CSA CE |

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Category | US10CP221127 |
|-------------------|---------------|
| Discount Schedule | 0CP2 |
| GTIN | 3606480278174 |
| Returnability | No |
| Country of origin | TW |

Packing Units

| • | |
|------------------------------|-----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.31 in (8.4 cm) |
| Package 1 Width | 1.57 in (4.0 cm) |
| Package 1 Length | 1.18 in (3.0 cm) |
| Package 1 Weight | 1.9 oz (55.0 g) |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 3.35 in (8.5 cm) |
| Package 2 Width | 2.45 in (6.22 cm) |
| Package 2 Length | 8.00 in (20.32 cm) |
| Package 2 Weight | 24.7 oz (700.5 g) |
| Unit Type of Package 3 | BB1 |
| Number of Units in Package 3 | 100 |
| Package 3 Height | 8.58 in (21.8 cm) |
| Package 3 Width | 12.87 in (32.7 cm) |
| Package 3 Length | 17.28 in (43.9 cm) |
| Package 3 Weight | 35.3 lb(US) (16.0 kg) |



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

| ⊘ Environmental footprint | | |
|--|---|--|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 1 | |

Use Better

| Materials and Substances | |
|--|--|
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | Yes |
| China RoHS Regulation | China RoHS declaration |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Use Again

| ○ Repack and remanufacture | |
|----------------------------|--|
| Circularity Profile | No need of specific recycling operations |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Take-back | No |

Dimensions Drawings

Approximate Dimensions

