

# Climasys CC - electronic hygrostat - 200…240 V - Hr 20…80% - OLED screen

NSYCCOHY230VID

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Range	ClimaSys
Product name	ClimaSys CC
Product or Component Type	Electronic hygrostat
Humidity setting range	2080 %
Display Type	OLED screen
Information Displayed	Relative humidity

## Complementary

Input voltage	200240 V AC	
Maximum switching capacity	4 A 230 V AC	
Electrical connection	6 terminals 2.5 mm <sup>2</sup>	
Mounting Mode	By screws Clipped	
Height	External: 3.3 in (85 mm)	
Width	External: 2.2 in (56 mm)	
Depth	External : 1.7 in (44 mm)	
Mounting Location	On mounting plate Cross rails 35 mm DIN rail Spacial upright	
Ambient Air Temperature for Operation	-40176 °F (-4080 °C)	
Hysteresis	3 %	
Number of outputs	2 heating function	
Material	PC	
Color	Light gray	
Flame retardance	Self-extinguishing conforming to UL94 (material V0)	
Product Certifications	UR	

# Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
GTIN	3606480152634
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin CN

# **Packing Units**

•		
Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	2.28 in (5.800 cm)	
Package 1 Width	2.95 in (7.500 cm)	
Package 1 Length	3.43 in (8.700 cm)	
Package 1 Weight	5.432 oz (154.000 g)	
Unit Type of Package 2	CAR	
Number of Units in Package 2	75	
Package 2 Height	10.63 in (27.000 cm)	
Package 2 Width	11.93 in (30.300 cm)	
Package 2 Length	17.72 in (45.000 cm)	
Package 2 Weight	25.463 lb(US) (11.550 kg)	
Unit Type of Package 3	PAM	
Number of Units in Package 3	900	
Package 3 Height	36.61 in (93.000 cm)	
Package 3 Width	39.37 in (100.000 cm)	
Package 3 Length	47.24 in (120.000 cm)	
Package 3 Weight	330.694 lb(US) (150.000 kg)	

# **Contractual warranty**

	<del>-</del>	
Coverage	Core product	
Warrantv	18 months	



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

# ∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

#### **Use Better**

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
SCIP Number	3452f1a3-f13d-4adf-84ba-2572bcc8e35c
REACh Regulation	REACh Declaration

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.