

Panel mounted timer monofunction, Harmony XB5, plastic, 22mm, time delay 3...60min, 24V DC

XB5DTB25

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony XB5
Product or Component Type	Timer
Sale per indivisible quantity	1

Complementary

Bezel material	Plastic		
Fixing collar material	Plastic		
Mounting diameter	0.9 in (22 mm)		
Panel Thickness	0.040.2 in (16 mm)		
Shape of signaling unit head	Round		
Time delay range	360 min		
Time delay type	A		
Repeat accuracy	+/- 0.5 %		
Setting accuracy of time delay	+/- 10 % of full scale 77 °F (25 °C) IEC 61812-1		
Temperature Drift	+/- 0.05 %/°C		
Voltage drift	+/- 0.2 %/V		
Protection Type	Reverse polarity protection Overvoltage protection		
Pollution degree	3 IEC 60664-1		
Output Type	Open collector PNP		
Temporary permissible current	10 A 0.01 s		
minimum switching current	10 mA		
Voltage drop in closed state	3 V		
Nominal rating	200 mA at 68 °F (20 °C)(derating 1.5 mA per °C)		
Residual current in open state	0.1 mA		
Power Consumption in W	1 W		
Reset time	5 ms after time delay on de-energisation 7 ms during time delay on de-energisation		
Local signalling	LED green, flashing timing in progress LED, steady no timing in progress and output relay energised		
[Us] rated supply voltage	24 V DC		
Supply voltage limits	16.831.2 V DC		
Output short-circuit protection	Yes		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Connections - terminals	Screw terminals 1 x 4 mm² IEC 60947-1 Screw terminals 1 x 2.5 mm² IEC 60947-1		
IP degree of protection	IP65 front: conforming to IEC 60529 IP20 back: conforming to IEC 60529		
Ambient Air Temperature for Operation	-4140 °F (-2060 °C)		
Ambient Air Temperature for Storage	-4176 °F (-2080 °C)		
Tightening torque	4.4 lbf.in (0.5 N.m)		
Dielectric strength	1500 V IEC 61812-1		
[Ui] rated insulation voltage	50 V IEC 60947-1 50 V IEC 60664-1		
[Uimp] rated impulse withstand voltage	4 kV IEC 60947-1 4 kV IEC 60664-1		
Surge withstand	1 kV, level 2 IEC 61000-4-5		
Overvoltage category	Class 3 conforming to IEC 60536 Class 3 conforming to IEC 60664-1		
Vibration resistance	0.15 mm (f= 1060 Hz) conforming to IEC 60068-2-6 2 gn (f= 60150 Hz) conforming to IEC 60068-2-6		
Shock resistance	+/- 15 gn 11 ms 6 shocks on each axis)IEC 60068-2-27		
Resistance to fast transients	2 kV level 3 IEC 61000-4-4		
Electromagnetic compatibility	Electrostatic discharge 6 kV level 3 conforming to IEC 61000-4-2 Electromagnetic emission class B conforming to IEC 55011		
Resistance to electromagnetic fields	9.1 V/m (10 V/m) 80 MHz1 GHz level 3 IEC 61000-4-3 2.7 V/m (3 V/m) 1.42 GHz level 2 IEC 61000-4-3 0.9 V/m (1 V/m) 22.7 GHz level 1 IEC 61000-4-3		
Immunity to radioelectric fields	10 V level 3 IEC 61000-4-6		
Disturbance radiated/conducted	Class B EN 50022		
Standards	UL 508 IEC 61812-1		
Product Certifications	UL Listed CE		
Device presentation	Monolithic product		
Height	2.4 in (62 mm)		
Width	1.1 in (29 mm)		
Depth	1.1 in (29 mm)		
Net Weight	0.060 lb(US) (0.027 kg)		
Diameter	1.1 in (29 mm)		

Ordering and shipping details

Category	US10CS200028
Discount Schedule	0CS2
GTIN	3606481205490
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1	1
Package 1 Height	1.26 in (3.2 cm)
Package 1 Width	1.26 in (3.2 cm)
Package 1 Length	2.95 in (7.5 cm)
Package 1 Weight	1.06 oz (30.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	32.1 oz (911.0 g)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better


Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Dimensions Drawings

Dimensions




- (e) Clamping thickness: 1 mm to 6 mm / 0.03 in. to 0.24 in. (1) Sealing ring
- (2) Screw

XB5DTB25

Mounting and Clearance

Panel Cut-out for Analog Timer (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors



(1) Diameter on finished panel or support

(2) Ø22 mm recommended (Ø22.3 0+0.4) / Ø0.89 in. recommended (Ø0.88 in. 0^{+0.016})


(2) 922 min recommended (922.3 0+0.4) / 90.69 m. recommended (90.66 m. 0				
Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	50	1.97	30	1.18

Product data sheet

XB5DTB25

Connections and Schema

Wiring Diagram



 ${\bf T}: {\sf Timer}$

(1) Load A1 - A2 : Supply (24VDC)

XB5DTB25


Technical Description


Function A : On Delay Timer

Description

The timing period T begins on energisation with blinking LED indication. After timing, the output (18) closes and LED goes steady

Function: Output







(A1- A2) Supply

Technical Illustration


Dimensions





Technical Illustration

Wiring diagram



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony XB5



Offer Marketing Illustration

Product benefits / Features



Product data sheet

XB5DTB25

Image of product / Alternate images

Alternative





