


COAXIAL CONNECTOR, SMA, 50 Ohm, Straight panel cable jack (female), flange mount

25_SMA-50-2-25/111_N

Properties

- Excellent return loss
- Intermateable with PC3.5 and SK
- Applicable in frequencies up to 18 GHz



Product configuration		
Interface type	Gender	Standard
SMA	jack	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data	
Weight	0.0019 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	soldered

Environmental data	
Operation temperature	-65 °C ... 165 °C

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight panel cable jack (female), flange mount

25_SMA-50-2-25/111_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22641493	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22641493	25_SMA-50-2-25/111_NE	Single

Suitable cables	
Cable group	Y3 - 2 mm / 50 Ohm
	Y16 - 2 mm / 50 Ohm
	Y11 - 2 mm / 50 Ohm
Suitable cables	SUCOFORM_86
	MULTIFLEX_86
	SR_86_TP_M17

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22544715	74_Z-0-0-68	Knives / Blades
23024588	74_Z-0-0-442	Soldering tool
23021264	74_Z-0-0-368	Locator
22643028	74_Z-0-0-164	Trimming tool
22643029	74_Z-0-0-157	Cable stripping tool
23019268	74_Z-0-0-364/---_-E	Support
23019269	74_Z-0-0-365	Support

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2469 / Date of publication: 11.07.2025 / uncontrolled copy