

# Single contact block, Harmony XB4, silver alloy, faston connector, 1NO

ZBE1013

Product availability: Stock - Normally stocked in distribution facility

#### Main

Range of Product	Harmony XB5 Harmony XB4
Product or Component Type	Contact block
Device short name	ZBE
Sale per indivisible quantity	5
IP degree of protection	IP20 IEC 60529
Contact operation	Slow-break
Contact block type	Single
Contacts usage	Standard contacts
Connections - terminals	Faston connector 1 x 6.35 mm Faston connector 2 x 2.8 mm

## Complementary

Net Weight	0.024 lb(US) (0.011 kg)
Contacts type and composition	1 NO
Positive opening	Without
Operating travel	0.1 in (2.6 mm) NO changing electrical state) 0.2 in (4.3 mm) total travel)
Operating force	2.3 N NO changing electrical state
Mechanical durability	10000000 cycles
Contacts material	Silver alloy (Ag/Ni)
[Ui] rated insulation voltage	250 V 3)IEC 60947-1
Mounting of block	Front mounting

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Electrical composition code	C1 9)
	C2 7)
	C3 6)
	C4 4)
	C5 5)
	C6 3)
	C7 4)
	C8 2)
	C9 3)
	C12 6)
	M1 6)
	M2 4)
	M3 4)
	M5 2)
	M6 2)
	M7 6)
	M8 4)
	M9 2)
	SF1 3)
	SF2 2)
	MF1 2)
	MF2 2)
	C10 2)
	M4 2)
	C13 1)

## **Environment**

Protective treatment	<del>-</del>	
Protective treatment	TH	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature for Operation	-40158 °F (-4070 °C)	
Standards	IEC 60947-5-4	
	JIS C8201-5-1	
	UL 508	
	CSA C22.2 No 14	
	IEC 60947-1	
	IEC 60947-5-1	
	JIS C8201-1	
Product Certifications	BV	
	UL	
	CSA	
	DNV	
	LROS (Lloyds register of shipping)	
Vibration resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27	

## Ordering and shipping details

	· · · · ·
Category	US10CS222469
Discount Schedule	0CS2
GTIN	3389110816358
Returnability	Yes
Country of origin	FR

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.20 in (5.6 cm)
Package 1 Width	1.73 in (4.4 cm)

Package 1 Length	2.13 in (5.4 cm)
Package 1 Weight	0.4 oz (10 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	2.20 in (5.6 cm)
Package 2 Width	1.73 in (4.4 cm)
Package 2 Length	2.13 in (5.4 cm)
Package 2 Weight	2.08 oz (59 g)
Unit Type of Package 3	S02
Number of Units in Package 3	400
Package 3 Height	5.91 in (15 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	11.07 lb(US) (5.02 kg)

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

<b>⊘</b> Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

#### Offer Marketing Illustration

#### Product benefits / Features

## **Technical Benefits**

#### Harmony XB4



#### Offer Marketing Illustration

#### **Product benefits / Features**



Image of product / Alternate images

#### **Alternative**











