

COAXIAL ADAPTER, PC 3.5, 50 Ohm, plug / plug (male / male)

32_PC35-50-0-2/199_N

Properties

- Precision interfaces
- Excellent electrical performance
- Premium base materials and platings

**Product configuration**

Interface type	Gender	Standard
PC 3.5	plug (male)	IEC 60169-23
PC 3.5	plug (male)	IEC 60169-23

Interface and material data

PC 3.5		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Stainless steel	
Body	Stainless steel	
Insulator	Air Dielectric - Bead - PS	
Coupling nut	Stainless steel	
PC 3.5		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Stainless steel	
Body	Stainless steel	
Insulator	Air Dielectric - Bead - PS	
Coupling nut	Stainless steel	

Electrical data

Impedance	50 Ω
Interface frequency	33 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 1.5 GHz	35 dB	1.036
1.5 GHz ... 6 GHz	30 dB	1.065

COAXIAL ADAPTER, PC 3.5, 50 Ohm, plug / plug (male / male)
32_PC35-50-0-2/199_N

Electrical Data (frequency related)			
Frequency range		Return loss	VSWR
6 GHz ... 18 GHz		20 dB	1.22
Mechanical data			
Weight		0.0071 kg	
Mating cycles		500	
Environmental data			
Operation temperature		-60 °C ... 100 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23020457	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
23020457	32_PC35-50-0-2/199_NE		Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2290 / Date of publication: 12.07.2025 / uncontrolled copy