

COAXIAL ADAPTER, 7/16 - N, 50 Ohm, plug / jack (male / female)

33_716-N-50-3/133_W

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
7/16	plug (male)	IEC 61169-4_CECC 22190_DIN 47223_VG 95250
N	jack (female)	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data		
7/16		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
N		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	7.5 GHz

Mechanical data	
Weight	0.0944 kg
Mating cycles	500

COAXIAL ADAPTER, 7/16 - N, 50 Ohm, plug / jack (male / female)

33_716-N-50-3/133_W

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
22658823	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table

Item number	Item description	Packaging type
22658823	33_716-N-50-3/133_WE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2263 / Date of publication: 12.07.2025 / uncontrolled copy