

COAXIAL ADAPTER, 7/16-precision - N, 50 Ohm, plug / jack (male / female)
33_716-N-50-51/-33_N

Properties

- Precision interfaces
- Excellent electrical performance
- Premium base materials and platings



Product configuration		
Interface type	Gender	Standard
7/16-precision	plug (male)	HUBER+SUHNER-716
N-precision	jack (female)	IEC 60169-16_MIL-STD-348A/402_CECC 22210

Interface and material data		
7/16-precision		
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
N-precision		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	7.5 GHz
VSWR	DC - 7.5 GHz (≤ 1.03 + 0.004 f GHz)

Mechanical data	
Weight	0.1141 kg
Mating cycles	500

COAXIAL ADAPTER, 7/16-precision - N, 50 Ohm, plug / jack (male / female)

33_716-N-50-51/-33_N

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
22544125	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table

Item number	Item description	Packaging type
22544125	33_716-N-50-51/-33_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2262 / Date of publication: 12.07.2025 / uncontrolled copy