

Pilot light, Harmony XVL, plastic, red, 8mm, protruding LED, faston connectors, 24V DC

XVLA134

Product availability: Stock - Normally stocked in distribution facility

Main

mann			
Range of Product	Harmony XVL		
Product or Component Type	LED pilot light with black bezel		
Component name	XVL		
Mounting diameter	0.3 in (8 mm)		
Light source	Protruding LED		
Light block colour	Red		
Protection Type	Built-in by diode Integral ballast resistor		
[Us] rated supply voltage	24 V		
IP degree of protection	IP40 IEC 60529 IP40 NF C 20-010		

Complementary

Supply circuit type	DC
Connections - terminals	Tag for Faston connectors 2.8 x 0.5 mm Tag for soldering connectors
Current Consumption	18 mA
[Ui] rated insulation voltage	50 V IEC 60947-1
Bulb lifespan	100000 h
Nominal voltage limit	0.81.1 Un
Terminals description ISO n°1	(X1-X2)PL
Height	0.5 in (12 mm)
Width	0.5 in (12 mm)
Depth	1.3 in (34 mm)
Net Weight	0.007 lb(US) (0.003 kg)

Environment

Product Certifications	UL CSA
Protective treatment	TC
Ambient air temperature for operation	-13158 °F (-2570 °C)
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Overvoltage category	Class 3 conforming to IEC 60536 Class 3 conforming to NF C 20-030

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10CS222460
Discount Schedule	0CS2
GTIN	3389110651089
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.47 in (1.2 cm)
Package 1 Width	0.47 in (1.2 cm)
Package 1 Length	1.65 in (4.2 cm)
Package 1 Weight	0.1 oz (3 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	1.18 in (3 cm)
Package 2 Width	4.33 in (11 cm)
Package 2 Length	4.33 in (11 cm)
Package 2 Weight	1.09 oz (31 g)
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Height	5.91 in (15 cm)
Package 3 Width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	18.0 oz (509 g)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	1	

Use Better

Materials and Substances	
Packaging without single use plastic	No
China RoHS Regulation	China RoHS declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	No

Dimensions Drawings

LED Pilot Light

Dimensions



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.

С		Ø	
mm	in.	mm in.	
32	1.26	12	0.47


Product data sheet

XVLA134

Mounting and Clearance

LED Pilot Light

Panel Drilling



Ø mi	Ø min G min		Ø min			H min	
mm	in.	mm	in.	mm	in.		
8.2	0.32	12.5	0.49	12.5	0.49		

Technical Illustration

Dimensions

