

Editable voice alarms, Harmony XVS, white, mounting 96mm DIN rail, NPN, 12...24V DC

XVSV9BWN

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony XVS
Product or Component Type	Editable electronic alarm
Beacon or indicator bank unit type	Sound unit
Device short name	XVSV

Complementary

Color	White	
Input type	Bit 6 channel input Binary 63 channel input	
Assembly style	Ready assembled	
Material	PC (polycarbonate): body PC (polycarbonate): back cover TPE (thermoplastic elastomer): front panel NBR (nitrile butadiene rubber)	
Marking	CE	
Overvoltage category	Class II conforming to IEC 61140	
Mounting Support	96 mm DIN rail	
[Us] rated supply voltage	1224 V DC	
[Ue] rated operational voltage	1030 V DC	
[Ui] Rated Insulation Voltage	250 V	
Inrush current	30 A	
Associated fuse rating	1 A	
[Uimp] rated impulse withstand voltage	2.5 kV IEC 60947-1	
Power Consumption in W	3.8 W	
Current consumption	160 mA 24 V DC	
Clamping Connection Capacity	<= 1 x 1.5 mm²	
Device Application	Packaging Printing Subway	
Mounting diameter	4.1 in (105 mm)	
Width	4.1 in (105 mm)	
Height	4.1 in (105 mm)	
Depth	2.0 in (50.1 mm)	
Net Weight	0.591 lb(US) (0.268 kg)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Discrete output type	NPN	
Signalling type	Adjustable vocal sound	
Standards	IEC 60947-5-1	
Protective treatment	TC	
Ambient Air Temperature for Storage	-4140 °F (-2060 °C)	
Ambient Air Temperature for Operation	14131 °F (-1055 °C)	
Pollution degree	2	
Relative humidity	3585 % without condensation	
Vibration resistance	7 gn	
IP degree of protection	Panel mounted IP65 IEC 60529 Wall mounted IP20	
Noise level	097 dB stop or suppress)1 m	

Ordering and shipping details

Category	US100XV22617
Discount Schedule	00XV
GTIN	3606480623905
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.13 in (10.5 cm)
Package 1 Width	1.97 in (5 cm)
Package 1 Length	4.13 in (10.5 cm)
Package 1 Weight	9.5 oz (268 g)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better


Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Fe0ee3ab-dd49-4abe-bd8e-c49754e2c442
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.

Use Again

○ Repack and remanufacture		
Take-back	No	

Dimensions Drawings

Dimensions




(t): Waterproof rubber (1.6 mm / 0.06 in.)

Product data sheet

XVSV9BWN

Mounting and Clearance


Panel Cut Dimensions



(1) Installation panel

Α	В	С
92 +0.6/0 mm (3.62 +0.0236/0 in.)	92 +0.6/0 mm (3.62 +0.0236/0 in.)	14 mm (0.040.15 in.)


Wall Mount Dimensions



(1) Installation panel

Connections and Schema


Wiring Diagram



- (1) Green
- (2) Yellow
- (3) Brown
- (4) Blue
- (5) Purple
- (6) Gray
- (7) White
- (8) Black
- (9) Red
- (10) Fuse (Rated current:1 A)


Technical Illustration

Dimensions



Technical Illustration

Wiring diagram



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony XVSV



XVSV9BWN

Offer Marketing Illustration

Product benefits / Features



Image of product / Alternate images

Alternative









Image of product in real life situation

