

COAXIAL ADAPTER, UHF - BNC, X Ohm, plug / jack (male / female)
33_UHF-BNC-0-1/032_-

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
UHF	plug (male)	IEC 60169-12
BNC	jack (female)	IEC 61169-8_MIL-STD-348A/301_CEECC 22120

Interface and material data		
UHF		
Piece parts	Material	Plating
Centre contact	Bronze	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PP (Polypropylene)	
Coupling nut	Brass	Nickel Plating
BNC		
Piece parts	Material	Plating
Centre contact	Bronze	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Interface frequency	0.2 GHz

Mechanical data	
Weight	0.0228 kg
Mating cycles	500

COAXIAL ADAPTER, UHF - BNC, X Ohm, plug / jack (male / female)

33_UHF-BNC-0-1/032_-

Environmental data

Operation temperature	-25 °C ... 100 °C
-----------------------	-------------------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
23013454	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c

Ordering Information Table

Item number	Item description	Packaging type
23013454	33_UHF-BNC-0-1/032_-E	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2135 / Date of publication: 12.07.2025 / uncontrolled copy