

COAXIAL SURGE PROTECTOR DEVICE, GDT technology up to 2.5 GHz

3402.41.0037

Properties

- Broadband frequency operation from DC to 2.5 GHz
- Gas discharge tube replaceable and not included
- DC/AC remote powering via coaxial same cable
- Surge current handling capability 30 kA once and 20 kA multiple
- Semper self-extinguishing functionality optional

**Product configuration**

Main path connectors	Port 1: unprotected, 7/16 plug (male) Port 2: protected, 7/16 jack (female)
Mounting and grounding	MH74 (bulkhead mounting), M8 (screw)
Side of bulkhead	protected side
EMP can be install reversed	YES

Interface and material data

Housing material / plating	Brass / SUCOPLATE (R) Plating
Center contact, material / plating	Port 1: Brass / Silver Plating Port 2: Copper Beryllium Alloy / Silver Plating

Electrical data

Impedance	50 Ω
Frequency frame	0 MHz to 2500 MHz
Return loss typical	≥ 20 dB
Insertion loss typical	≤ 0.2 dB
CW power frame	≤ 150 W
Residual pulse energy (typ.)	350 μ J (test pulse 4 kV 1.2/50 μ s; 2 kA 8/20 μ s)
Residual pulse voltage (typ.)	650 V (test pulse 4 kV 1.2/50 μ s; 2 kA 8/20 μ s)
Surge current handling capability	30 kA single, 20 kA multiple (test pulse 8/20 μ s)

Electrical remarks

Gas tube	Yes DC, GDT not included
Electrical remarks	Data refer to GDT 9071.99.0547, 230 V

COAXIAL SURGE PROTECTOR DEVICE, GDT technology up to 2.5 GHz
3402.41.0037

Mechanical data	
Weight	450 g
Mating cycles	500

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	IP65
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. D
Moisture resistance according	MIL-STD-202, Method 106

Compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23000127	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 3147-75-9 2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)
			CAS: 7439-92-1 Lead

Ordering Information Table	
Item number	Item description
23000127	3402.41.0037

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1996 / Date of publication: 28.02.2025 / uncontrolled copy