

interface plug-in relay, Harmony electromechanical relays, 16A, 1CO, 12V DC

RSB1A160JD

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony Electromechanical Relays
Series name	RSB series
Product or Component Type	Plug-in relay
Relay Type	Interface relay
Contacts type and composition	1 C/O
Status LED	Without
[Uc] control circuit voltage	12 V DC
Control Type	Without lockable test button
[Ithe] conventional enclosed thermal current	16 A -40104 °F (-4040 °C)

Complementary

•	
Average resistance	360 Ohm AC 20 °C +/- 10 %
[Ue] rated operational voltage	8.418 V DC
[Uimp] rated impulse withstand voltage	3.6 kV IEC 61000-4-5
[le] rated operational current	16 A AC-1/DC-1) NO IEC 8 A AC-1/DC-1) NC IEC
[Ui] rated insulation voltage	400 V IEC 60947
Maximum switching voltage	300 V DC IEC
Drop-out voltage threshold	>= 0.1 Uc DC
Load current	16 A 250 V AC 16 A 28 V DC
minimum switching current	10 mA
Maximum switching capacity	4000 VA/448 W
minimum switching voltage	12 V
Minimum switching capacity	120 mW 10 mA, 12 V
Operating time	20 ms operating 20 ms reset
Mechanical durability	30000000 cycles
Electrical durability	100000 cycles, 16 A at 250 V, AC-1 NO 100000 cycles, 8 A at 250 V, AC-1 NC
Safety reliability data	B10d = 100000
Operating rate	<= 600 cycles/hour under load <= 18000 cycles/hour no-load

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Average coil consumption	0.45 W DC
Removable legend	Without
Protection category	RT I
Operating position	Any position
Test levels	Level A group mounting
Device presentation	Complete product
Sale per indivisible quantity	10
Contacts material	Silver alloy (AgNi)
Shape of pin	Flat (PCB type)
Net Weight	0.031 lb(US) (0.014 kg)
Compatibility code	RSB

Environment

Dielectric strength	1000 V AC between contacts 2500 V AC between poles 5000 V AC between coil and contact	
Vibration resistance	+/- 1 mm (f= 1055 Hz) conforming to IEC 60068-2-6	
IP degree of protection	IP40 conforming to IEC 60529	
Ambient air temperature for operation	-40185 °F (-4085 °C) DC)	
Standards	CSA C22.2 No 14 IEC 61810-1 UL 508	
Product Certifications	EAC UL CSA	
Ambient Air Temperature for Storage	-40185 °F (-4085 °C)	
Shock resistance	10 gn 11 ms) not operating IEC 60068-2-27 5 gn 11 ms) in operation IEC 60068-2-27	

Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3389110254440
Returnability	No
Country of origin	AT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.83 in (2.100 cm)
Package 1 Width	0.98 in (2.500 cm)
Package 1 Length	12.24 in (31.100 cm)
Package 1 Weight	0.459 oz (13.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	0.83 in (2.100 cm)
Package 2 Width	0.98 in (2.500 cm)
Package 2 Length	12.24 in (31.100 cm)
Package 2 Weight	5.044 oz (143.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	350
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	5.91 in (15.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	11.621 lb(US) (5.271 kg)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	6
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	45b41055-6c52-408d-9c0c-5c663b810f29
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again


○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Product data sheet

RSB1A160JD


Dimensions Drawings

Dimensions



Connections and Schema

Wiring Diagram




(1) Before wiring please refer to the Instruction sheet

RSB1A160JD

Performance Curves

Electrical Durability of Contacts


Durability (inductive load) = durability (resistive load) x reduction coefficient. Resistive AC load



X Switching capacity (kVA)


Y Durability (Number of operating cycles)

Reduction coefficient for inductive AC load (depending on power factor $\cos \varphi$)



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC


Jul 12, 2025

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.

Technical Illustration

Dimensions

mm in.








Image of product / Alternate images

Alternative










Image of product in real life situation

