


COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub
technology with integrated high-pass filter
3407.17.0054

Properties

- Residual voltage reduced by 80 % compared to standard types of series 3400
- Residual energy reduced of more than 99.9 % compared to series 3401 and 3402
- DC-blocking on protected side of the device
- Available for applications from 70 MHz to 18 GHz
- Return loss 20 dB min. and Insertion loss 0.2 dB max.



Product configuration	
Main path connectors	Port 1: unprotected, N plug (male) Port 2: protected, N jack (female)
Mounting and grounding	MH12 (bulkhead mounting), M8 (screw), brk (bracket)
Side of bulkhead	protected side
EMP can be install reversed	YES

Interface and material data	
Housing material / plating	Brass / SUCOPLATE (R) Plating Port 1: Brass / Gold Plating (without Nickel underplating) Port 2: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)
Center contact, material / plating	

Electrical data	
Impedance	50 Ω
Frequency frame	140 MHz to 180 MHz
Return loss typical	20 dB
Insertion loss typical	0.2 dB
CW power frame	500 W
Residual pulse energy (typ.)	0.03 μJ (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs)
Surge current handling capability	50 kA multiple (test pulse 8/20 μs)

Electrical remarks	
Gas tube	No DC / shorted QW or LC

COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub technology with integrated high-pass filter

3407.17.0054

Mechanical data	
Weight	428 g
Mating cycles	500
Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP65, according to IEC 60529
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. A
Moisture resistance according	MIL-STD-202, Method 106
Ordering Information Table	
Item number	Item description
23003513	3407.17.0054

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1962 / Date of publication: 31.10.2024 / uncontrolled copy