

Head for push button, Harmony 9001K, metal, metal mushroom 60mm, red, 30mm, 2 positions, push pull

9001KR9RM95

Product availability: Stock - Normally stocked in distribution facility

Main

| Range of Product | Harmony 9001K |
|---------------------------|--------------------------------|
| Product or Component Type | Head for push-button |
| Product Compatibility | Contact block 9001KA |
| Device short name | 9001K |
| Type of operator | push-pull |
| Operator profile | Red mushroom Ø 60 mm, unmarked |

Complementary

| Bezel material | Metal |
|---------------------------------|-------------------------------|
| Mounting diameter | 1.2 in (30 mm) |
| CAD overall width | 2.4 in (60 mm) |
| CAD overall height | 2.4 in (60 mm) |
| CAD overall depth | 2.9 in (74 mm) |
| Net Weight | 0.33 lb(US) (0.15 kg) |
| Operating position | Any position |
| Shape of signaling unit head | Round |
| Head material | Metal |
| Operator additional information | Screw-on metal with set screw |
| Operator position information | 2 positions |
| Contacts type and composition | Without contact block |
| Mechanical durability | 5000000 cycles |
| Device presentation | Basic element |
| Cap/operator or lens colour | Red |
| Operator profile | Mushroom Ø 60 mm |
| Type of operator | Push-pull |
| Size | 30 mm |

Environment

| Protective treatment | тс |
|-------------------------------------|----------------------|
| Ambient Air Temperature for Storage | -40158 °F (-4070 °C) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Ambient Air Temperature for Operation | -13158 °F (-2570 °C) | | |
|--|---|--|--|
| Overvoltage category | Class II conforming to IEC 61140 | | |
| IP degree of protection | IP66 IEC 60529 | | |
| NEMA degree of protection | NEMA 1 | | |
| | NEMA 12 | | |
| | NEMA 13 | | |
| | NEMA 2 | | |
| | NEMA 3 | | |
| | NEMA 3R | | |
| | NEMA 4 | | |
| | NEMA 6 | | |
| Standards | IEC 60947-5-1 | | |
| | IEC 60947-1 | | |
| | IEC 60947-5-4 | | |
| | JIS C 4520 | | |
| | JIS C 852 | | |
| | UL 508 | | |
| | CSA C22.2 No 14 | | |
| Product Certifications | NEMA | | |
| | UL 508 | | |
| Vibration resistance | 7 gn (f= 2500 Hz) conforming to IEC 60068-2-6 | | |
| Shock resistance | 50 gn IEC 60068-2-27 | | |

Ordering and shipping details

| Category | US10CS121426 |
|-------------------|--------------|
| Discount Schedule | 0CS1 |
| GTIN | 785901981480 |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| Unit Type of Package 1 | PCE |
|------------------------------|----------------------|
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.90 in (4.826 cm) |
| Package 1 Width | 2.20 in (5.588 cm) |
| Package 1 Length | 3.70 in (9.398 cm) |
| Package 1 Weight | 5.440 oz (154.221 g) |

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

| Packaging made with recycled cardboard | Yes |
|--|---|
| Packaging without single use plastic | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| SCIP Number | Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d |
| REACh Regulation | REACh Declaration |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Use Again


| ○ Repack and remanufacture | |
|----------------------------|--|
| Take-back | No |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Product data sheet

9001KR9RM95

Dimensions Drawings

Dimensions



 \boldsymbol{e} panel thickness: 1 to 6 mm / 0.04 to 0.24 in.


a 28 mm / 1.10 in.

9001KR9RM95

Mounting and Clearance

Contact Block Mounting Position


Top and Rear views



- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

Panel Cut-Out


Clearance




| Legend plate | a min. | | b min. | |
|--------------|--------|------|--------|------|
| | mm | in. | mm | in. |
| 9001KN2•• | 57.2 | 2.25 | 57.2 | 2.25 |
| 9001KN3•• | 57.2 | 2.25 | 57.2 | 2.25 |

Individual Cut-outs Details

2 alternatives





9001KR9RM95

Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony 9001K

