


COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub technology with integrated high-pass filter

3407.17.0085

Properties

- Residual voltage reduced by 80 % compared to standard types of series 3400
- Residual energy reduced of more than 99.9 % compared to series 3401 and 3402
- DC-blocking on protected side of the device
- Available for applications from 70 MHz to 18 GHz
- Return loss 20 dB min. and Insertion loss 0.2 dB max.
- Broad-band design
- Space saving desing



Product configuration

Main path connectors	Port 1: unprotected, N plug (male) Port 2: protected, N jack (female)
Mounting and grounding	MH170 (bulkhead mounting), brk (bracket)
Side of bulkhead	protected side
Inline design	YES
EMP can be install reversed	YES

Interface and material data

Housing material / plating	Aluminium / Chromatized
Center contact, material / plating	Port 1: Brass / Gold Plating (without Nickel underplating) Port 2: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)

Electrical data

Impedance	50 Ω
Frequency frame	2000 MHz to 6000 MHz
Return loss typical	≥ 20 dB
Insertion loss typical	≤ 0.2 dB
CW power frame	≤ 300 W
Residual pulse energy (typ.)	0.1 nJ LEMP (test pulse 4 kV 1.2/50 μ s; 2 kA 8/20 μ s) 20 nJ (test pulse 55 kA 8/20 μ s)
Residual pulse voltage (typ.)	0.5 V LEMP (test pulse 4 kV 1.2/50 μ s; 2 kA 8/20 μ s)

COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub technology with integrated high-pass filter

3407.17.0085

Electrical data			
		5 V (test pulse 55 kA 8/20 µs)	
Surge current handling capability		50 kA multiple (test pulse 8/20 µs)	
Electrical remarks			
Gas tube		No DC / shorted QW or LC	
Mechanical data			
Weight		108 g	
Mating cycles		100	
Environmental data			
Operation temperature		-40 °C ... 85 °C	
Storage temperature		-40 °C ... 85 °C	
Ingress protection (IP Rating)		Mated / IP68, according to IEC 60529	
Thermal shock according		MIL-STD-202, Method 107, Cond. B	
Vibration according		MIL-STD-202, Method 204, Cond. A	
Moisture resistance according		MIL-STD-202, Method 106	
Compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84092556	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number		Item description	
84092556		3407.17.0085	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-PI959 / Date of publication: 28.02.2025 / uncontrolled copy