

Illuminated push-button head, Harmony 9001SK, plastic, plastic guard flush, red, 30mm, spring return, LED red, 120V

9001SK1L38LRR

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony 9001SK	
Product or Component Type	Head for illuminated push-button	
Device short name	9001SK	
Type of operator	spring return	
Operator profile	Red flush, unmarked	
Operator additional information	Plastic guard	
Light block supply	Direct 120 V AC/DC	

Complementary

•		
Bezel material	Plastic	
Mounting diameter	1.2 in (30 mm)	
Shape of signaling unit head	Octagonal	
Light source	Red LED	
Bulb base	BA 9s	
[Us] rated supply voltage	120 V AC/DC	
Contacts type and composition	Without contact block	
Connections - terminals	Screw clamp terminals 1 x 0.222 x 1.5 mm² EN/IEC 60947-1	
Tightening torque	7.08 lbf.in (0.8 N.m) EN/IEC 60947-1	
Shape of screw head	Cross slotted	
Mechanical durability	5000000 cycles	
Operating position	Any position	
[le] rated operational current	0.55 A 125 V, DC-13, A600-Q600 NEMA	
[Ui] rated insulation voltage	250 V 3)EN/IEC 60947-1	
[Uimp] rated impulse withstand voltage	2.5 kV EN/IEC 60947-1	
Positive opening	Without	
Short-circuit protection	10 A cartridge fuse EN/IEC 60947-5-1	
[Ith] conventional free air thermal current	10 A	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[lcm] rated short-circuit making	12 kA 600 V AC-15, 7200 VA	
capacity	15 kA 480 V AC-15, 7200 VA	
	30 kA 240 V AC-15, 7200 VA	
	60 kA 120 V AC-15, 7200 VA	
	0.27 kA 250 V DC-13	
	0.55 kA 125 V DC-13	
	0.1 kA 600 V DC-13	
Rated breaking capacity	1.2 kA 600 V AC-15, 720 VA	
	1.5 kA 480 V AC-15, 720 VA	
	3 kA 240 V AC-15, 720 VA	
	6 kA 120 V AC-15, 720 VA	
	0.27 kA 250 V DC-13	
	0.55 kA 125 V DC-13	
	0.1 kA 600 V DC-13	
Net Weight	0.399 lb(US) (0.181 kg)	
Device presentation	Basic element	
Cap/operator or lens colour	Red	
[Us] rated supply voltage	120 V	
Light source colour	Red	
Type of operator	Spring return	
Operator profile	Flush	

Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-5-4 UL 508 EN/IEC 60947-5-1 JIS C 4520
	JIS C 852 CSA C22.2 No 14
Product Certifications	UL 508 NEMA
Protective treatment	TC
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Ambient air temperature for operation	-13158 °F (-2570 °C)
Vibration resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn IEC 60068-2-27
Electrical shock protection class	Class II IEC 61140
IP degree of protection	IP66 IEC 60529
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3 NEMA 4 NEMA 4

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
GTIN	785901490296
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	2.10 in (5.334 cm)
Package 1 Length	3.60 in (9.144 cm)
Package 1 Weight	6.400 oz (181.437 g)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Materials and Substances	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
China RoHS Regulation	China RoHS declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	No