

COAXIAL ADAPTER, SK, 50 Ohm, Bulkhead, jack / jack (female / female)

34_SK-50-0-51/199_N

Properties

- Precision interfaces
- Excellent electrical performance
- Premium base materials and platings



Product configuration		
Interface type	Gender	Standard
SK	jack (female)	MIL-STD-348A/323
SK	jack (female)	MIL-STD-348A/323

Interface and material data		
SK		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Stainless steel	
Body	Stainless steel	
Insulator	PPE (Polyphenylene ether, PPO)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
SK		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Stainless steel	
Body	Stainless steel	
Insulator	PPE (Polyphenylene ether, PPO)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	40 GHz
VSWR	DC - 40 GHz (≤ 1.02 + 0.01 f GHz)

COAXIAL ADAPTER, SK, 50 Ohm, Bulkhead, jack / jack (female / female)

34_SK-50-0-51/199_N

Mechanical data	
Weight	0.0042 kg
Mating cycles	500

Environmental data	
Operation temperature	-40 °C ... 125 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22658969	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22658969	34_SK-50-0-51/199_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2091 / Date of publication: 12.07.2025 / uncontrolled copy