

Pendant control station, Harmony XAC, plastic, yellow, pistol grip, 2 push buttons with NO+NC, 1 emergency stop NC

XACA2053

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range of Product	Harmony XAC	
Product or Component Type	Pendant control station	
Device short name	XACA pistol grip	

#### Complementary

Control station type	Double insulated	
Enclosure Material	Polypropylene	
Control Type	Intuitive	
Electrical circuit type	Control circuit	
Enclosure Type	Complete ready for use	
Control station application	Control of single speed hoist motor	
Control station composition	2 push-buttons + 1 emergency stop	
Control button type	Stop push-button Ø 30 mm 1 NC latching First push-button 1 NC + 1 NO raise, slow Second push-button 1 NC + 1 NO lower, slow	
Product compatibility	ZB2BE102 for emergency stop ZB2BE102 + ZB2BE101 for each direction	
Mechanical interlocking	With mechanical interlocking	
Control station colour	Yellow	
Connections - terminals	Screw clamp terminals, 1 x 2.5 mm <sup>2</sup> with or without cable end	
	Screw clamp terminals, 2 x 1.5 mm <sup>2</sup> with or without cable end	
Standards	Screw clamp terminals, 2 x 1.5 mm² with or without cable end  IEC 60204-32 CSA C22.2 No 14 IEC 60947-5-1 UL 508	
Standards Product Certifications	IEC 60204-32 CSA C22.2 No 14 IEC 60947-5-1	
	IEC 60204-32 CSA C22.2 No 14 IEC 60947-5-1 UL 508	
Product Certifications	IEC 60204-32 CSA C22.2 No 14 IEC 60947-5-1 UL 508 UL CSA	
Product Certifications  Protective treatment  Ambient Air Temperature for	IEC 60204-32 CSA C22.2 No 14 IEC 60947-5-1 UL 508 UL CSA	
Product Certifications  Protective treatment  Ambient Air Temperature for Operation  Ambient Air Temperature for	IEC 60204-32 CSA C22.2 No 14 IEC 60947-5-1 UL 508 UL CSA TH -13158 °F (-2570 °C)	
Product Certifications  Protective treatment  Ambient Air Temperature for Operation  Ambient Air Temperature for Storage	IEC 60204-32 CSA C22.2 No 14 IEC 60947-5-1 UL 508 UL CSA TH -13158 °F (-2570 °C) -40158 °F (-4070 °C)	
Product Certifications  Protective treatment  Ambient Air Temperature for Operation  Ambient Air Temperature for Storage  Vibration resistance	IEC 60204-32 CSA C22.2 No 14 IEC 60947-5-1 UL 508  UL CSA TH  -13158 °F (-2570 °C)  -40158 °F (-4070 °C)  15 gn (f= 10500 Hz) conforming to IEC 60068-2-6	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

IK degree of protection	IK08 conforming to IEC 62262	
Mechanical durability	1000000 cycles	
Cable entry	Rubber sleeve with stepped entry 0.30.6 in (715 mm)	
Contact code designation	A600 AC-15, Ue = 240 V, Ie = 3 A IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A IEC 60947-5-1 appendix A	
[Ithe] conventional enclosed thermal current	10 A	
[Ui] rated insulation voltage	600 V 3)IEC 60947-1	
[Uimp] rated impulse withstand voltage	6 kV IEC 60947-1	
Contact operation	Slow-break	
Maximum resistance across terminals	25 MOhm	
Operating force	1315 N	
Short-circuit protection	10 A fuse protection cartridge gG	
Rated operational power in W	40 W DC-13 1000000 cycles 60 cyc/mn 120 V 0.5 inductive IEC 60947-5-1 appendix C 48 W DC-13 1000000 cycles 60 cyc/mn 48 V 0.5 inductive IEC 60947-5-1 appendix C 65 W DC-13 1000000 cycles 60 cyc/mn 24 V 0.5 inductive IEC 60947-5-1 appendix C	
Terminals description ISO n°1	(13-14)NO (11-12)NC	
Terminals description ISO n°2	(11-12)NC	
Terminal identifier	(13-14)NO (11-12)NC	
Net Weight	0.75 lb(US) (0.34 kg)	

# Ordering and shipping details

Category	US10CS222473	
Discount Schedule	0CS2	
GTIN	3389110558814	
Returnability	No	
Country of origin	FR	

## **Packing Units**

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	2.56 in (6.500 cm)	
Package 1 Width	4.57 in (11.600 cm)	
Package 1 Length	13.19 in (33.500 cm)	
Package 1 Weight	12.769 oz (362.000 g)	
Unit Type of Package 2	S03	
Number of Units in Package 2	15	
Package 2 Height	11.81 in (30.000 cm)	
Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	

Package 2 Weight	13.009 lb(US) (5.901 kg)	
Unit Type of Package 3	P06	
Number of Units in Package 3	120	
Package 3 Height	29.53 in (75.000 cm)	
Package 3 Width	23.62 in (60.000 cm)	
Package 3 Length	31.50 in (80.000 cm)	
Package 3 Weight	127.612 lb(US) (57.884 kg)	

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	2
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Materials and Substances	
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

#### **Alternative**









### **Product data sheet**

### XACA2053



