

COAXIAL ADAPTER, 7/16, 50 Ohm, T-style, 3 jacks (female)

46_716-50-0-1/003_-

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
7/16	jack (female)	IEC 61169-4_CECC 22190_DIN 47223_VG 95250
7/16	jack (female)	IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Interface and material data		
7/16		
Piece parts	Material	Plating
Centre contact	Bronze / Brass	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
7/16		
Piece parts	Material	Plating
Centre contact	Bronze / Brass	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	7.5 GHz

COAXIAL ADAPTER, 7/16, 50 Ohm, T-style, 3 jacks (female)
46_716-50-0-1/003_-

Mechanical data			
Weight		0.2589 kg	
Mating cycles		500	
Environmental data			
Operation temperature		-65 °C ... 165 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22643266	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22643266	46_716-50-0-1/003_-E		Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1902 / Date of publication: 12.07.2025 / uncontrolled copy