



Main

Range of product	TeSys
Range	TeSys
Device short name	DE1D
Product or Component Type	Enclosure
Material	Polycarbonate
Device composition	Contacteur ordered separately Thermal overload relay ordered separately
Product Compatibility	LE1D18...35
Control type	Push-button reset Blue R Selector switch 2 positions start/stop O-I

Complementary

Cable entry number	2 ISO20 top 2 ISO20 bottom 2 Pg 16 bottom 2 ISO25 top 2 Pg 21 bottom 2 ISO25 bottom
Height	7.91 in (201 mm)
Width	4.06 in (103 mm)
Depth	6.69 in (170 mm)
Product Weight	1.10 lb(US) (0.5 kg)

Environment

IP degree of protection	IP65 IEC 60529
IK degree of protection	IK07 IEC 60529
Ambient air temperature for operation	23...104 °F (-5...40 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	18401 - WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
GTIN	3389110087154
Nbr. of units in pkg.	1
Package weight(Lbs)	23.28 oz (660 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.71 in (14.5 cm)
Package 1 width	6.30 in (16 cm)
Package 1 Length	8.27 in (21 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------