CA2KN22B7

Control relay, TeSys K, 2 NO + 2 NC, It or eq to 690V, 24VAC coil





Main

Range	TeSys
Product name	TeSys CAK
Product or Component Type	Control relay
Device short name	CA2K
Contactor application	Control circuit
Utilisation category	DC-13 AC-15
Pole contact composition	2 NO + 2 NC
[Ue] rated operational voltage	<= 690 V <= 400 Hz
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	24 V AC 50/60 Hz

Complementary

Complementary	
[lth] conventional free air thermal current	10 A 122 °F (50 °C)
Irms rated making capacity	110 A IEC 60947
Associated fuse rating	10 A gG IEC 60947 10 A gG VDE 0660
[Ui] rated insulation voltage	690 V IEC 60947 750 V VDE 0110 group C 690 V BS 5424 600 V CSA C22.2 No 14
Mounting Support	Plate Rail
Connections - terminals	Screw clamp terminals 1 0.000.01 in² (1.54 mm²)solid Screw clamp terminals 2 0.000.01 in² (1.54 mm²)solid Screw clamp terminals 1 0.000.01 in² (0.754 mm²)flexible with cable end Screw clamp terminals 2 0.000.01 in² (0.754 mm²)flexible without cable end Screw clamp terminals 1 0.000.00 in² (0.341.5 mm²)flexible without cable end Screw clamp terminals 2 0.000.00 in² (0.341.5 mm²)flexible without cable end
Tightening torque	11.51 Lbf.In (1.3 N.m) screw clamp terminals Philips No 2 11.51 Lbf.In (1.3 N.m) screw clamp terminals flat Ø 6 mm 11.51 lbf.in (1.3 N.m) screw clamp terminals pozidriv No 2
Control circuit voltage limits	Drop-out 0.20.75 Uc 122 °F (50 °C)) Operational 0.81.15 Uc 122 °F (50 °C))
Operating time	1020 ms coil de-energisation and NO opening 1020 ms coil energisation and NO closing 1525 ms coil de-energisation and NC closing 515 ms coil energisation and NC opening
Mechanical durability	10 Mcycles
Maximum operating rate	10000 cyc/h
Immunity to microbreaks	2 ms
Inrush power in VA	30 VA 68 °F (20 °C))
Hold-in power consumption in VA	4.5 VA 68 °F (20 °C))
Heat dissipation	1.3 W
Minimum switching voltage	17 V
Minimum switching current	5 mA
Non overlap distance	0.02 in (0.5 mm)
Insulation resistance	> 10 MOhm
Height	2.28 in (58 mm)

Width	1.77 in (45 mm)	
Depth	2.24 in (57 mm)	
Net Weight	0.40 lb(US) (0.18 kg)	

Environment

Standards	EN/IEC 60947-4-1
	GB/T 14048.4
	UL 60947-4-1
	CSA C22.2 No 60947-4-1
	JIS C8201-4-1
Product Certifications	CB Scheme
	CCC
	UL
	CSA
	EAC
	CE
	UKCA
IP degree of protection	IP2X
Protective treatment	TC IEC 60068
Ambient Air Temperature for Operation	-13122 °F (-2550 °C)
Ambient Air Temperature for Storage	-58176 °F (-5080 °C)
Operating altitude	6561.68 ft (2000 m) without derating
Flame retardance	V1 conforming to UL 94
	Requirement 2 conforming to NF F 16-101
	Requirement 2 conforming to NF F 16-102
Mechanical robustness	Vibrations contactor open2 Gn, 5300 Hz IEC 60068-2-6
	Vibrations contactor closed4 Gn, 5300 Hz IEC 60068-2-6
	Shocks contactor open10 Gn for 11 ms IEC 60068-2-27
	Shocks contactor closed15 Gn for 11 ms IEC 60068-2-27

Ordering and shipping details

Category	22371-RELAYS, CONTROL
Discount Schedule	112
GTIN	3389110500271
Returnability	Yes
Country of origin	ID

Packing Units

Packing Units	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	2.44 in (6.2 cm)
Package 1 Length	1.93 in (4.9 cm)
Package 1 Weight	6.35 oz (180.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	20.54 lb(US) (9.316 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	800
Package 3 Height	30.31 in (77.0 cm)
Package 3 Width	31.50 in (80.0 cm)
Package 3 Length	23.62 in (60.0 cm)
Package 3 Weight	335.10 lb(US) (152.0 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☑ REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EEU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	☑ China RoHS Declaration
RoHS exemption information	₫Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------