

SMX3000LVNCUS

APC Smart-UPS X, Line Interactive, 3kVA,
Rack/tower convertible 4U, 120V, 6x 5-15R
+3x 5-20R+1x L5-30R NEMA, NMC, Extended
runtime, Short depth, TAA



Overview

Lead time Usually Ships within 2 Weeks



Main

Main Input Voltage	120 V
Other Input Voltage	100 V 110 V 127 V
Main Output Voltage	120 V
Other Output Voltage	100 V 110 V 127 V
Kw Rating	2700 W
Rated power in VA	2880 VA
Input Connection Type	NEMA L5-30P
Nb of power socket outlets	6 NEMA 5-15R 3 NEMA 5-20R 1 NEMA L5-30R
Number of rack unit	4U
Cable length	8 ft (2.44 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack Mounting brackets Rack Mounting support rails Removable support feet Smart UPS signalling RS-232 cable USB cable Web/SNMP Management Card

General

Number of power module	2400
Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	TAA compliance
Redundant	No

Physical

Color	Black
Height	17.01 in (43.2 cm)
Width	7.01 in (17.8 cm)
Depth	19.02 in (48.3 cm)
Net Weight	85.19 lb(US) (38.64 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	1
USB compatible	Yes

Input

Efficiency at full load	70...153 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	2880 VA
Max Configurable Power (Watts)	2700 W
Maximum output current	15 A
Transfer Time	2-4 ms 4ms typical : 8ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	BSMI CSA NOM TAA compliance TÜV VCCI Class A
Equipment protection policy	Lifetime : \$150000
Standards	EN 50091-2 EN 55022 Class A FCC Part 15 class A UL 1778

Environmental

Acoustic level	55 dBA
Heat dissipation	276 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1

Battery Life	3...5 year(s)
Battery power in VAH	738 VAh runtime
Battery Charge Power (Watts)	245 W rated
Battery option	SMX120BP 1 2214 VAh SMX120BP 2 3690 VAh SMX120BP 3 5166 VAh SMX120BP 4 6642 VAh SMX120BP 6 9594 VAh SMX120BP 8 12546 VAh SMX120BP 10 15498 VAh

Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators Multi-function LCD status and control console
Emergency Power Off (EPO)	Yes
Free slots	0
Pre-Installed SmartSlot™ Cards	Network management card 2 with environmental monitoring

Surge Protection and Filtering

Surge energy rating	540 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	731304340409
Package weight(Lbs)	105.23 lb(US) (47.73 kg)

Packing Units

Package 1 Height	12.99 in (33 cm)
Package 1 width	23.07 in (58.6 cm)
Package 1 Length	24.92 in (63.3 cm)
Number of Units in Package 3	6
Package 3 Weight	856.92 lb(US) (388.69 kg)
Package 3 Height	43.50 in (110.49 cm)
Package 3 width	48.00 in (121.92 cm)
Package 3 Length	31.00 in (78.74 cm)
Pallet unit layers	2
Pallet layers	4

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional extended warranties available, optional on-site warranties available
----------	--