



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Battery Type	Gel Cell
Provided Equipment	User Manual

Physical

Height	8.58 in (21.8 cm)
Width	6.81 in (17.3 cm)
Depth	12.99 in (33 cm)
Net Weight	68.41 lb(US) (31.03 kg)
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	UL Recognized
Marking	CE Mark

Environmental

Ambient Air Temperature for Operation	-4...131 °F (-20...55 °C)
Ambient Air Temperature for Storage	-4...122 °F (-20...50 °C)

Batteries & Runtime

Battery blocks per string	4
Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Stand alone battery stack
Battery Voltage	12 V

Ordering and shipping details

GTIN	731304322221
Package weight(Lbs)	70.00 lb(US) (31.75 kg)

Packing Units

Package 1 Height	10.98 in (27.9 cm)
Package 1 width	7.99 in (20.3 cm)
Package 1 Length	14.02 in (35.6 cm)

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------