


MOUNTING LAYOUT FOR TWO CLIPS




L = .383 [9.73] FOR MINI FUSES

L = .530 [13.46] FOR STANDARD AND LOW PROFILE FUSES



THIS DOCUMENT IS THE PROPERTY OF
KEYSTONE ELECTRONICS CORP. AND
SHALL NOT BE REPRODUCED, DISTRIBUTED
OR USED AS A BASIS FOR MANUFACTURE
WITHOUT PRIOR WRITTEN PERMISSION
FROM KEYSTONE ELECTRONICS CORP.

ACTUAL SIZE



9.10.24	NO CHANGES TO PART.	J
11.20.20	ECN 20-093 H1 WAS .005/.000	H
10.23.19	CHANGE AS PER ECN19-079	G
3.11.19	CHANGE AS PER ECN19-032	F
2.05.19	CHANGE AS PER ECN19-018	E
3.22.17	CHANGE AS PER ECR 17-014	D
12.04.14	CHANGE AS PER ECN 14-117	C
9.06.12	CHANGE AS PER ECN 12-130	B
5.11.07	CHANGE AS PER ECN 07-022	A
DATE	DESCRIPTION	REV.

NOTE:

K FILE NUMBER: E354010

KEYSTONE ELECTRONICS CORP.

www.keyelco.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500

PART NAME

LOW PROFILE UNIVERSAL PC AUTO FUSE CLIP

MATERIAL

.016 [0.41] TH'K BRASS

FINISH

TIN NICKEL PLATE

DRN BY

BOONE

DATE

2.13.07

APP'D

RH

SCALE

5X

TOLERANCES

INCH [MM]

DECIMAL

± .005 [± 0.13]

ANGULAR

± 1°

UNLESS OTHERWISE SPECIFIED

CODE

C

DWG NO.

3557