








A		B	C	D	E	F	G
MD	Description	Please follow Pulse Limits for the hazardous substances (RoHS, halogens) in the document "Pulse Hazardous Substances (HS) Limits (RPG002-03)" and "Vendor Survey Questionnaire, Material Composition (LDM-SAF-L0040)".		Reliability Test Spec according to WIHS7.5.33 (Reliability Test Working Instruction) Default test standard is Test Standard A if no definition			
P2	Change the Logo						



- NOTES:UNLESS OTHERWISE SPECIFIED
1. DIM. MARKED ▼ TO BE CHECKED.
 2. MATERIAL: Ycut-FX-EH THICKNESS T=0.10mm
 3. NO CRACK APPEARS ON CONTACT BALL SHAPE.
 4. NO LINES APPEARS ON BENDING AREA.
 5. ALL UNSPECIFIED RADII TO BE 0.05 MAXIMUM .
 6. BURR:0.03MAX;CUMBER:1.5MM MAX/500MM; TWIST:20°/500MM.
 7. PRE-LOAD FORCE:0.40N ON CONTACT POINT
 8. PLATING: 3u" Min GOLD PLATING ON CONTACT AREA,
1u" Min GOLD PLATING ON SOLDER AREA,
50u" MIN NICKEL PLATING OVER ALL



RECOMMENDED PCB LAYOUT
DEFAULT TOLERANCE IS ±0.05MM



STATE AT WORKING HIGHT 2.50

Confidential
This is a proprietary information of Pulse Suzhou.
No reproduction/copying is allowed without permission.

Functional Characteristics Key <Cpk requirement : Cpk> >
 ◆ Process Capability Studies required< total pcs >
 ◆ Ongoing Statistical Process Control Required < total pcs >
 ◆ Critical dimension need to be measured, no CPK requirement < total pcs >

- .X± 0.15
- .XX± 0.10
- .XXX±0.05
- X:± 5°

PULSE (SUZHOU) WIRELESS PRODUCTS CO.LTD.		THIRD ANGLE PROJECTION		SHEET NUMBER		1 / 1			
 99 HUOJU RD. SUZHOU NEW DISTRICT 215009 P.R.CHINA		SCALE 4.000		GENERAL TOLERANCE					
				CUSTOMER NUMBER					
				DESIGN	JACKIE	JUN-28-18			
PRODUCT(S) SW0182N		DOCUMENT NUMBER SW0182N		CHECKED	MARK	Nov-22-17			
				APPROVED	JAMES	Nov-22-17			
ITEM TX80103-001(CLIP)		PART VERSION P01		DOCUMENT VERSION P2		P2	March-07-19	CHRIS	
				P1		JUN-28-18	JACKIE		
				MOD	DATE		NAME		