


Y Splitter Cable for Select Battery Packs, Blue 175A DC Connectors, 1 ft. (0.3 m)

MODEL NUMBER: 48VDCSPLITTER



Connects two Tripp Lite BP48V24-2U and other select external battery packs to a compatible UPS system to extend runtime.

Description

The 48VDCSPLITTER Y Splitter Cable connects two external battery packs to a compatible UPS system to extend runtime. It is compatible with the non-expandable BP48V24-2U and other select battery packs that specify compatibility with this cable. The one-foot (0.3-meter) 48VDCSPLITTER is constructed using 4 AWG two-conductor black cabling. It features three blue 175A DC connectors: two outputs for the battery packs and one input for a UPS system that specifies the use of a BP48V24-2U battery pack.

Features

Connects 2 Select Battery Packs to a Compatible UPS System

- Compatible with BP48V24-2U and other select battery packs that specify compatibility with this cable
- Heavy-duty 4 AWG 2-conductor black cabling
- 3 blue 175A DC connectors (2 output, 1 input)
- 1-ft. (0.3 m) in length

Specifications

OVERVIEW	
UPC Code	037332158468
Accessory Type	Extender
Accessory Class	UPS Accessories
INPUT	
Input Connection Type	175A Blue 48V DC Connector (1)
OUTPUT	

Highlights

- Heavy-duty 4 AWG 2-conductor black cabling
- 3 blue 175A DC connectors (2 output, 1 input)
- 1-ft. (0.31 m) in length

Package Includes

- 48VDCSPLITTER Y Splitter Cable, 1-ft. (0.31 m)



Powering Business Worldwide

TRIPP LITE
SERIES

Output Connector Type	175A Blue 48V DC Connector (2)
PHYSICAL	
Cable Length (ft.)	1
Cable Length (m)	0.30
Shipping Dimensions (hwd / in.)	10.00 x 10.00 x 4.00
Shipping Dimensions (hwd / cm)	25.40 x 25.40 x 10.16
Shipping Weight (lbs.)	2.00
Shipping Weight (kg)	0.91
Unit Weight (lbs.)	2
Unit Weight (kg)	0.91
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.