

Universal Dual-Monitor Mount Adapter

MODEL NUMBER: DMA1327SD



Dual-monitor kit converts a single-monitor display mount so it will hold 2 flat-screen 13-27 in. monitors at the same time.

Features

Mount 2 Flat-Screen Monitors on One Display Mount This dual-monitor mount securely attaches to your current display mount, allowing you to use two monitors simultaneously without taking up any additional desk or table space in your workstation. Ideal for home, school or office use, the VESA-compliant adapter fits most flat-panel monitors, televisions and other displays from 13 to 27 inches.

Easy to Adjust to Your Liking With a Single Touch Just one touch is all it takes to adjust the monitors' viewing angles and heights to fit your comfort level. The monitors tilt from -15° to +15° to give you flexibility in minimizing glare and providing comfortable viewing from multiple angles. They also rotate 360 degrees for viewing in portrait or landscape orientation.

Each VESA Mount Supports Up to 22 pounds (9.9 kg) This dual-monitor kit mounts to your current display mount's 75 x 75 mm, 75 x 100, 100 x 75 mm or 100 x 100 mm VESA plate. Made from durable steel, the adapter features a scratch-resistant black powder-coated finish that blends with your décor and stands up to frequent handling. Mounting hardware is included. Keep in mind that the total mount weight must not exceed the maximum weight of the single display mount.

5-Year Warranty and Environmentally Responsible Design The DMA1327SD comes with a 5-year warranty. It's manufactured in compliance with strict RoHS specifications.

Highlights

- Mounts to current single-display mount to leave valuable desk or table space clear
- Each mount supports up to 22 lbs (9.9 kgs) and flat-screen displays from 13 to 27 in.
- Scratch-resistant powder-coated finish blends into your workspace décor
- Monitors tilt from -15° to +15° and rotate 360° to customize the ideal viewing angle
- Total weight must not exceed the max weight of the single monitor display mount

Applications

- Use 2 displays side-by-side for easier multitasking, editing multiple documents and watching video across screens

Package Includes

- (2) VESA head brackets
- Mounting plate
- (2) VESA bracket bars
- Bracket bar coupler
- (2) End caps
- (2) Cable hooks
- (2) End cap screws
- (4) M6 x 30 screws
- (8) M4 x 12 screws
- (12) M5 x 12 screws
- (12) D5 washers
- (4) M5 nuts
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332212764
Device Compatibility	Monitor/HDTV
Accessory Type	Dual Bar Mount
Accessory Class	Display Mount Accessories



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Full
Mounting Location	Desktop; Desk Clamp
Degrees of Motion	-15/+15 Tilt; 360 Rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	22
Maximum Weight Capacity (kg)	10
Number of Displays	2
Unit Dimensions (hwd / in.)	31.700 x 4.700 x 5.300
Unit Dimensions (hwd / cm)	31.7 x 4.7 x 5.3
Unit Weight (lbs.)	5.4
Unit Weight (kg)	2.45
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
IP68 Rated	No
IP20 Rated	No
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.