


AVERY DENNISON MARKETING SPECIFICATION

HISTORY

REV.	DATE	DESCRIPTION
F	10-16-08	UPDATE MODEL AND UPDATE OPERATING TEMPERATURE.

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.



MOUNTING:	Ø 6.60 ± 0.25MM HOLE AND 6.35MM HEX HOLE IN 7.0MM MAXIMUM THICK PANEL
TENSILE STRENGTH:	50 LBF / 22.7 KGF MIN.
OPERATING TEMP RANGE:	-40°F (-40°C) TO 257°F (125°C)
WEIGHT:	1.8 GRAMS EACH
BUNDLE DIAMETER:	Ø 1/16" [1.6mm] TO Ø 1-3/4" [44.5mm]
INSTALLATION TOOL:	12001 - HAND TOOL 12500 - PNEUMATIC TOOL
TOOL TENSION SETTING:	6 - 8
PACKAGING:	500/BAG, 10 BAGS/MASTER

APPROVALS:

ENG. APPR.	<i>[Signature]</i> 10/16/08
Q.A. APPR.	<i>[Signature]</i> 10-17-08

SPECIFIED TOLERANCES	INCHES	[MM]
.XX ± .03	.X ± .7	
.XXX ± .01	.XX ± .25	
ANGULAR:	± 2°	

MATERIAL	IMPACT MODIFIED NYLON 6/6
COLOR	BLACK



FASTENER DIVISION
FITCHBURG, MA 01420 U.S.A.
TEL. 1-800-225-5913
FAX. 978-353-8157

DESCRIPTION	7 FLUTE CURVED TIE
STOCK NO.	20038
REV.	F