


AVERY DENNISON MARKETING SPECIFICATION

TOLERANCES IN. = .030 IN.
MM = 0.7 mm



NOT TO SCALE

TENSILE STRENGTH: (LOOPE)	50 LBSF. / 22.7 KG. MINIMUM PER MIL-S-23190.
OPERATING TEMP. RANGE:	-40°F (-40°C) TO 220°F (105°C)
MATERIAL:	IMPACT MODIFIED NYLON 6/6 PER ASTM D4066 - HEAT STABILIZED, BLACK
WEIGHT:	1.8 GRAMS
BUNDLE DIAMETER:	1/16" - 1-3/4"
MOUNTING:	8MM PUNCHED HOLE, M10 THREADED HOLE
APPLICATION TOOL:	12001 - HAND INSTALLATION TOOL 12500 - PNEUMATIC INSTALLATION TOOL
TOOL TENSION SETTING:	6-8
PACKAGED IN:	500/BAG, 10 BAGS/MASTER



**AVERY
DENNISON**

FASTENER DIVISION
FITCHBURG, MA 01420 U.S.A.
TEL. 1-800-225-5913
MA. 978-353-8157

DESCRIPTION:

CURVED TIE, 8MM, 4 FLUTE, BLACK

APPROVALS:

Q.A:

ENG'RG:

STOCK NO.

20094

REV.

B