

# Product Data Sheet

PD-0053-A

**3M™ Mini D Ribbon (MDR)**

**Connector**

**MDR Surface Mount**

**Right Angle Receptacle**

**102XX-1210 XE**

**102XX-1S10 XE**

---

**3M Electronic Solutions Division**

6801 River Place Blvd.  
Austin, TX 78726-9000



---

## Table of Contents

|     |   |    |
|-----|---|----|
| 1.0 | SCOPE.....  | 2  |
| 2.0 | PRODUCT TESTED.....   | 2  |
| 3.0 | GENERAL CONDITIONS.....   | 2  |
| 3.1 | Test Specimens.....   | 2  |
| 3.2 | Standard Test Conditions.....   | 2  |
| 4.0 | TEST RESULTS SUMMARY.....   | 3  |
| 5.0 | TESTING.....  | 4  |
| 5.1 | General.....  | 4  |
|     | <i>Visual (Appearance)</i> .....  | 4  |
|     | <i>Contact Resistance — MIL-STD-202F Method 307</i> .....   | 4  |
| 5.2 | Environmental.....  | 5  |
|     | <i>Test Sequence #1</i> .....   | 5  |
|     | <i>Insertion/withdrawal (50 cycles)</i> .....   | 5  |
|     | <i>Moisture Resistance — MIL-STD-202F Method 106F</i> .....   | 5  |
|     | <i>Salt Atmosphere (Corrosion) — MIL-STD-202F Method 101D</i> .....   | 5  |
|     | <i>Test Sequence #2</i> .....   | 6  |
|     | <i>Thermal Shock — MIL-STD-202F Method 107G</i> .....   | 6  |
|     | <i>Humidity (Steady State) — MIL-STD-202F Method 103B</i> .....   | 6  |
|     | <i>Vibration — MIL-STD-202F Method 201A</i> .....   | 6  |
|     | <i>Test Sequence #3: Life (at Elevated Ambient Temperature) — MIL-STD-202F Method 108A</i> .....  | 7  |
|     | <i>H<sub>2</sub>S Gas Sequence</i> .....  | 7  |
|     | <i>Insertion/withdrawal (50 cycles)</i> .....   | 7  |
|     | <i>Hydrogen Sulfide Test for Electronic Equipment Connectors — JEIDA-38-1984</i> .....  | 8  |
| 5.3 | Mechanical.....   | 8  |
|     | <i>Mating and Unmating Forces — EIA-364-13A</i> .....   | 8  |
|     | <i>Durability</i> .....   | 8  |
|     | <i>Mechanical Shock — MIL-STD-202F Method 213B</i> .....  | 9  |
|     | <i>Solder Heat Resistance (Moisture/Reflow Sensitivity Classification for Nonhermetic Solid State Surface Mount Devices) — JEDEC J-STD-020C</i> ..... | 9  |
| 5.4 | Electrical.....   | 10 |
|     | <i>Dielectric Withstanding Voltage — MIL-STD-202F Method 301</i> .....  | 10 |
|     | <i>Insulation Resistance — MIL-STD-202F Method 302</i> .....  | 10 |
|     | IMPORTANT NOTICE.....   | 11 |

## 1.0 Scope

This data sheet summarizes test methods, test conditions and product performance for the 3M MDR Surface Mount Right Angle Receptacle 102XX-1XX0 XX.

## 2.0 Product Tested

|                               |  |
|-------------------------------|--|
| Product:                      | MDR Surface Mount Right Angle Receptacle |
| Product Number:               | 102XX-1210 XE, 102XX-1S10 XE             |
| Related Specification Sheets: | TS-0755, TS-2242                         |
| Mating Product:               | 3M MDR Wire Mount Plug                   |
| Mating Product Number:        | 101XX-6000 XX                            |

This test report applies to the MDR receptacles listed below, which have identical mating contact structure and plating specifications:

- 102XX-1210 VE, PE (Wiping Area Plating: 0.50  $\mu\text{m}$  [20  $\mu\text{m}$ ] Min. Gold)
- 102XX-1S10 VE, PE (Wiping Area Plating: 0.50  $\mu\text{m}$  [20  $\mu\text{m}$ ] Min. Gold)

## 3.0 General Conditions

### 3.1 Test Specimens

The test specimens shall be strictly in compliance with the design, construction details and physical properties detailed in the relevant Technical Specification Sheet (See Section 2).

### 3.2 Standard Test Conditions

The test shall be done under the following conditions:

|                       |                  |
|-----------------------|------------------|
| Temperature:          | 15°C to 35°C     |
| Relative Humidity:    | 45% to 75%       |
| Atmospheric pressure: | 650 to 800 mm Hg |

#### 4.0 Test Results Summary

| Items                |  | Specification   | Test Method  | Results |
|----------------------|--|---|--|---------|
| <b>General</b>       | Visual   | No defects such as deformation, blister, damage, crack, etc.  | Sumitomo 3M Design Spec  | Pass    |
|                      | Contact Resistance                                   | Max. R: < 50 mΩ   | MIL-STD-202F Method 307  | Pass    |
| <b>Environmental</b> | Moisture Resistance                                  | Max. Δ R: < ±25 mΩ<br>10 Cycles   | MIL-STD-202F Method 106F   | Pass    |
|                      | Salt Atmosphere (Corrosion)                          | No Physical abnormalities after test<br>Max. Δ R: < ±25 mΩ  | MIL-STD-202F Method 101D Condition B   | Pass    |
|                      | Thermal Shock  | No Physical abnormalities after test<br>Max. Δ R: < ±25 mΩ<br>5 Cycles, -55 °C to +85 °C  | MIL-STD-202F Method 107G Condition A   | Pass    |
|                      | Humidity (Steady State)                              | Max. Δ R: < ±25 mΩ<br>Conditions: 40° ±2°C<br>/ 90 – 95 %RH for 96 Hours  | MIL-STD-202F Method 103B, Condition B  | Pass    |
|                      | Life at Elevated Ambient Temperature (Thermal Aging) | No Physical abnormalities after test<br>Max. Δ R: < ±25 mΩ<br>85 °C for 1000 Hours  | MIL-STD-202F Method 108A, Condition D  | Pass    |
|                      | Hydrogen Sulfide Gas                                 | No Physical abnormalities after test<br>Max. Δ R: < ±25 mΩ<br>Conditions: H <sub>2</sub> S 3± 1 PPM, 40°C, 70–80 %RH for 96 hours | JEIDA-38-1984  | Pass    |
| <b>Mechanical</b>    | Vibration  | No Physical abnormalities after test<br>Max. Δ R: < ±25 mΩ<br>No electrical discontinuity > 1 μ sec                               | MIL-STD-202F Method 201A   | Pass    |
|                      | Mating and Unmating Forces                           | Mating force: 1.47N/pin Max<br>Unmating force: 0.39N/pin Min  | EIA-364-13A  | Pass    |
|                      | Durability   | Insertions/Withdrawals<br>Max. Δ R: < ±25 mΩ  | Sumitomo 3M Design Spec  | Pass    |
|                      | Mechanical Shock                                     | No Physical abnormalities after test<br>Max. Δ R: < ±25 mΩ<br>No electrical discontinuity > 1 μ sec                               | MIL-STD-202F Method 213B Condition A<br>Half sine, (11 milliseconds) 50 g ± X,Y,Z (9 total shocks) | Pass    |
|                      | Resistance To Soldering Heat                         | No Physical abnormalities after test.   | JEDEC J-STD-020C   | Pass    |
| <b>Electrical</b>    | Dielectric Withstanding Voltage                      | 500 VAC <sub>RMS</sub> @ Sea Level  | MIL-STD-202F Method 301  | Pass    |
|                      | Insulation Resistance                                | 500 MΩ @ 500 V <sub>DC</sub>  | MIL-STD-202F Method 302 Condition B  | Pass    |

## 5.0 Testing

Test methods are based upon Sumitomo 3M test procedures, the United States Department of Defense MIL-STD-202F, 1 April 1980, "Test Method Standard - Electronic And Electrical Component Parts" and the Japan Electronic Industry Development Association JEIDA-38-1984, "Hydrogen Sulphide Test for Electronic Equipment Connectors."

### 5.1 General

#### Visual (Appearance)

##### *Purpose*

The purpose of this test is to visually examine and dimensionally inspect the connector in order to determine whether the connector conforms to the applicable specification and detail documents not covered by performance requirements.

##### *Test Method*

The examination shall be made in accordance with Sumitomo 3M design specifications. The visual examination shall include inspection of the following features as a minimum: workmanship, marking, materials, finish, standards, design and construction. The dimensional inspection shall be a check for compliance with the outline drawings of the detail specification.

#### Contact Resistance — MIL-STD-202F Method 307

##### *Purpose*

The purpose of this test is to evaluate contact resistance characteristics of electrical contacts under conditions where applied voltages and currents do not alter the physical contact interface or modify the conductive oxide films which may be present.

##### *Test Method*

The low-signal level contact resistance shall be tested with circuit current of 1.5 mA and open circuit voltage of 20 mV maximum. The termination resistance includes contact to wire interface resistance, bulk resistance of contact, and resistance of solder joints of connectors to circuit boards. See Figure 1.




Figure 1. Contact resistance measurement method

##### *Test Results*

The initial readings are in milliohms. All other readings are the change in resistance from the initial reading in milliohms. All initial readings meet the specification requirement of less than 50 milliohms.

---

## 5.2 Environmental

### Test Sequence #1

#### Introduction

In this test sequence, initial contact resistance measurements are taken for a sample of connectors. The sample is then subjected to a series of three tests: Insertion/withdrawal (50 cycles), Moisture Resistance and Salt Atmosphere (Corrosion). Measurements are taken after each test to record the change in connection resistance (Delta-R). The results follow.

#### Insertion/withdrawal (50 cycles)

##### Purpose

The purpose of this test is to determine the effects of subjecting electrical connectors to a conditioning action of mating and unmating of connector simulating typical operation of the connector.

##### Test Method

The plug and receptacle were mated and un-mated manually 50 times at the approximate rate of one cycle per second. Contact resistance was measured at completion.

|            |           |
|------------|-----------|
| Condition: | 50 Cycles |
|------------|-----------|

#### Moisture Resistance — MIL-STD-202F Method 106F

##### Purpose

The purpose of this test is to evaluate, in an accelerated manner, the resistance of component parts and constituent materials to the deteriorative effects of the high-humidity and heat conditions typical of tropical environments. This test differs from the steady-state humidity test (Method 103B) and derives its added effectiveness in its employment of temperature cycling, which provides alternate periods of condensation and drying essential to the development of the corrosion processes and, in addition, produces a "breathing" action of moisture into partially sealed containers. Increased effectiveness is also obtained by use of a higher temperature, which intensifies the effects of humidity.

##### Test Method

Mated connectors shall be tested in accordance with MIL-STD-202F Method 106F.

|                    |                     |
|--------------------|---------------------|
| Temperature Cycle: | -10 °C to 65 °C     |
| Relative Humidity: | 90 – 100 %RH        |
| Duration:          | 10 Cycles (10 Days) |

#### Salt Atmosphere (Corrosion) — MIL-STD-202F Method 101D

##### Purpose

The purpose of this test is to determine the effects of a controlled salt laden atmosphere on the electrical connector.

##### Test Method

Mated connectors shall be tested in accordance with MIL-STD-202F Method 101D, Test Condition B.

|                |                              |
|----------------|------------------------------|
| Salt Solution: | 5 ±1%                        |
| Temperature:   | 35 °C±3 °C (95 °F<br>±5 °F). |
| Duration:      | 48 Hours                     |

*Test Results*

| N = 100             | Initial |  | I/W<br>(50 cycles) |       | Moisture<br>(10 cycles) |       | Salt Atmosphere<br>(48 hours) |       |
|---------------------|---------|--|--------------------|-------|-------------------------|-------|-------------------------------|-------|
|                     | R       |  | R                  | ΔR    | R                       | ΔR    | R                             | ΔR    |
| Maximum:            | 38.71   |  | 37.03              | 2.82  | 47.38                   | 12.41 | 53.83                         | 19.38 |
| Average:            | 34.93   |  | 34.85              | -0.07 | 35.14                   | 0.22  | 36.20                         | 1.27  |
| Minimum:            | 32.53   |  | 32.60              | -2.60 | 32.69                   | -2.98 | 32.72                         | -2.55 |
| Standard Deviation: | 1.44    |  | 1.04               | 1.33  | 1.96                    | 2.15  | 3.38                          | 3.41  |

**Test Sequence #2**

*Introduction*

In this test sequence, initial contact resistance measurements are taken for a sample of connectors. The sample is then subjected to a series of three tests: Thermal Shock, Humidity and Vibration. Measurements are taken after each test to record the change in connection resistance (Delta-R). The results follow.

**Thermal Shock — MIL-STD-202F Method 107G**

*Purpose*

The purpose of this test is to determine the resistance of a given electrical connector to exposure at extremes of high and low temperatures and to the shock of alternate exposures to these extremes, simulating the worst probable conditions of storage, transportation and application.

*Test Method*

Mated connectors shall be tested in accordance with MIL-STD-202F Method 107G, Test Condition A.

|                  |                             |
|------------------|-----------------------------|
| Temperature:     | -55 °C & +85 °C             |
| Cycle Time:      | 30 minutes each Temperature |
| Transition Time: | 5 minute maximum            |
| Cycles:          | 5                           |

**Humidity (Steady State) — MIL-STD-202F Method 103B**

*Purpose*

The purpose of this test is to permit evaluation of the properties of materials used in connectors as they are influenced or deteriorated by the effects of high humidity and heat condition.

*Test Method*

Mated connectors shall be tested in accordance with MIL-STD-202F Method 103B, Test Condition B.

|                    |             |
|--------------------|-------------|
| Temperature Range: | 40 ± 2 °C   |
| Relative Humidity: | 90 – 95 %RH |
| Duration:          | 96 Hours    |

**Vibration — MIL-STD-202F Method 201A**

*Purpose*

The purpose of this test is to determine the effects of vibration within the predominant or random vibration frequency ranges and magnitudes that may be encountered during the life of the connector.

*Test Method*

Mated connectors shall be tested in accordance with MIL-STD-202F Method 201A.

|            |   |
|------------|---|
| Amplitude: | 0.03 inch (0.06 inch max. total excursion)                                |
| Frequency: | 10 to 55 Hz   |
| Duration:  | 2 hours in each of 3 mutually perpendicular directions (total of 6 hours) |



*Test Results*

| <i>N</i> = 100      | Initial |       | Thermal Shock |       | Humidity (Steady State) |       | Vibration |    |
|---------------------|---------|-------|---------------|-------|-------------------------|-------|-----------|----|
|                     | R       | ΔR    | R             | ΔR    | R                       | ΔR    | R         | ΔR |
| Resistance (mΩ)     |         |       |               |       |                         |       |           |    |
| Maximum:            | 38.41   | 45.71 | 8.08          | 46.55 | 8.92                    | 46.99 | 9.44      |    |
| Average:            | 34.88   | 35.17 | 0.29          | 35.26 | 0.38                    | 35.86 | 0.98      |    |
| Minimum:            | 32.43   | 32.51 | -1.32         | 32.62 | -2.16                   | 32.81 | -0.46     |    |
| Standard Deviation: | 1.55    | 1.71  | 0.94          | 1.98  | 1.43                    | 2.34  | 1.42      |    |

**Test Sequence #3: Life (at Elevated Ambient Temperature) — MIL-STD-202F Method 108A**

*Introduction*

In this test sequence, initial contact resistance measurements are taken for a sample of connectors. The sample is then subjected to exposure to an elevated ambient temperature for a specified length of time. A sequence of contact resistance measurements are taken after 42, 180, 630 and 1000 hours to record the change in connection resistance (Delta-R). The results follow.

*Purpose*

The purpose of this test is to determine the effects on the electrical and mechanical characteristics of the connector resulting from exposure of the connector to an elevated ambient temperature for a specified length of time.

*Test Method*

Mated connectors shall be tested in accordance with MIL-STD-202F Method 108A, Test Condition D.

|              |            |
|--------------|------------|
| Temperature: | 85 °C      |
| Duration:    | 1000 hours |

*Test Results*

| <i>N</i> = 100      | Initial |       | 42 Hrs |       | 180 Hrs |       | 630 Hrs |       | 1000 Hrs |    |
|---------------------|---------|-------|--------|-------|---------|-------|---------|-------|----------|----|
|                     | R       | ΔR    | R      | ΔR    | R       | ΔR    | R       | ΔR    | R        | ΔR |
| Resistance, mΩ      |         |       |        |       |         |       |         |       |          |    |
| Maximum:            | 37.54   | 38.13 | 4.76   | 45.67 | 12.30   | 42.14 | 5.92    | 48.38 | 10.84    |    |
| Average:            | 34.26   | 34.53 | 0.27   | 34.98 | 0.72    | 34.84 | 0.58    | 35.22 | 0.95     |    |
| Minimum:            | 32.89   | 33.10 | -2.03  | 32.86 | -1.53   | 32.92 | -1.60   | 33.14 | -1.23    |    |
| Standard Deviation: | 0.94    | 1.06  | 0.81   | 1.84  | 1.57    | 1.37  | 1.05    | 1.97  | 1.48     |    |

**H<sub>2</sub>S Gas Sequence**

*Introduction*

In this test sequence, initial contact resistance measurements are taken for a sample of connectors. The sample is then subjected to a series of two tests: Insertion/withdrawal (50 cycles) and Hydrogen Sulfide Test for Electronic Equipment Connectors. Measurements are taken after each test to record the change in connection resistance (Delta-R). The results follow.

**Insertion/withdrawal (50 cycles)**

*Purpose*

The purpose of this test is to determine the effects of subjecting electrical connectors to a conditioning action of mating and unmating of connector simulating typical operation of the connector.

*Test Method*

The plug and receptacle were mated and un-mated manually 50 times at the approximate rate of one cycle per second. Contact resistance was measured at completion.

|            |           |
|------------|-----------|
| Condition: | 50 Cycles |
|------------|-----------|

### Hydrogen Sulfide Test for Electronic Equipment Connectors — JEIDA-38-1984

*Purpose*

The purpose of this test is to determine the effects of a controlled environmentally related corrosive atmosphere on the electrical connector.

*Test Method*

Mated connectors shall be tested in accordance with JEIDA-38-1984.

|                    |           |
|--------------------|-----------|
| Relative Humidity: | 70 – 80 % |
| Temperature:       | 40 ± 2 °C |
| Duration:          | 96 Hours  |
| H <sub>2</sub> S:  | 3 ± 1 ppm |

*Test Results*

| N = 100             | Initial | I/W<br>(50 cycles) |       | H <sub>2</sub> S |       |
|---------------------|---------|--------------------|-------|------------------|-------|
|                     |         | R                  | ΔR    | R                | ΔR    |
| Resistance (mΩ)     | R       | R                  | ΔR    | R                | ΔR    |
| Maximum:            | 38.17   | 37.14              | 2.35  | 37.26            | 1.42  |
| Average:            | 35.27   | 35.46              | 0.19  | 35.05            | -0.21 |
| Minimum:            | 33.13   | 33.25              | -2.83 | 33.27            | -3.03 |
| Standard Deviation: | 1.19    | 1.10               | 0.79  | 1.14             | 0.89  |

### 5.3 Mechanical

#### Mating and Unmating Forces — EIA-364-13A

*Purpose*

The purpose of this test is to determine the mechanical forces required to mate and unmate electrical connectors.

*Test Method*

Using the tensile tester, a 50-position plug is inserted in the receptacle at 5mm/minute. The maximum load is measured. In the removal test, the receptacle is removed from the plug at 5 mm/minute and the maximum load is measured.

*Test Results*

|           | Per connector   | Per contact    |
|-----------|-----------------|----------------|
| Force:    | N [kgf]         | N [gf]         |
| Mating:   | 43.1 [4.4] Max  | 0.86 [88] Max. |
| Unmating: | 26.5 [2.7] Min. | 0.53 [54] Min. |

### Durability

*Purpose*

The purpose of this test is to determine the effects of subjecting electrical connectors to a conditioning action of mating and unmating of connector simulating operations approximating the life of the connector.

*Test Method*

The plug and receptacle were mated and un-mated manually 500 times at the approximate rate of one cycle per second. Contact resistance was measured at completion.

|            |            |
|------------|------------|
| Condition: | 500 Cycles |
|------------|------------|

*Test Results*

| <i>N</i> = 100      | Initial R<br>(mΩ) | Final ΔR<br>(mΩ) |
|---------------------|-------------------|------------------|
| Maximum:            | 37.80             | 9.76             |
| Average:            | 34.30             | 0.43             |
| Minimum:            | 32.61             | -4.56            |
| Standard Deviation: | 1.18              | 1.40             |

**Mechanical Shock — MIL-STD-202F Method 213B**

*Purpose*

This test is conducted to determine the suitability of connectors when subjected to shocks such as those expected from rough handling, transportation and operation.

*Test Method*

Mated connectors shall be tested in accordance with MIL-STD-202F Method 213B, Test Condition A.

|                    |   |
|--------------------|---|
| Normal Duration:   | 11 milliseconds                         |
| Peak Acceleration: | 50 g                                    |
| Wave form:         | Half Sine                               |
| Cycles:            | 3 times each in +/- X, Y & Z directions |

*Test Results*

| <i>N</i> = 100      | Initial R<br>(mΩ) | Final ΔR<br>(mΩ) |
|---------------------|-------------------|------------------|
| Maximum:            | 28.88             | 14.86            |
| Average:            | 19.27             | 0.18             |
| Minimum:            | 4.90              | -9.64            |
| Standard Deviation: | 4.65              | 1.66             |

**Solder Heat Resistance (Moisture/Reflow Sensitivity Classification for Nonhermetic Solid State Surface Mount Devices) — JEDEC J-STD-020C.**

*Purpose*

The purpose of this standard is to identify the classification level of nonhermetic solid state surface mount devices (SMDs) that are sensitive to moisture-induced stress so that they can be properly packaged, stored, and handled to avoid damage during assembly solder reflow attachment and/or repair operations.

*Test Method*

Surface mount connectors shall be tested in accordance with JEDEC J-STD-020C.

Process: **Baking** → **Moisture soak** → **Reflow** → Room temp. → **Reflow** → Room temp. → **Reflow**

- (1) Pre-Treatment/Baking: 24 hours minimum at 125 +5/-0 °C.
- (2) Pre-Treatment/Moisture Soak: 85 °C/ 85% relative humidity for 168 +5/-0 hours.
- (3) Reflow Soldering: The samples are mounted on the board under the following soldering conditions.

Test Board: FR-4 or higher grade, 1.6mm thickness, thickness of copper foil 0.035 mm, with pre-flux treatment. Through hole diameter and land shape of each terminal were designed under each recommended pc board foot pattern.

Reflow: Preheat: 150 to 200 °C for 60 to 180 seconds  
 Soldering: more than 217 °C for 60 to 150seconds  
 Peak 255 to 260 °C for 20 to 40seconds

*Test Results*

| TEST                   | TEST CONDITION<br>(JEDEC J-STD-020C)      | SAMPLE        | RESULT     |           |
|------------------------|---|---------------|------------|-----------|
|                        |   |               | Appearance | Wiper Gap |
| Solder Heat Resistance | Bake<br>Moisture Soak<br>Reflow – 3 times | 102XX-1210 XE | Passed     | Passed    |
|                        |   | 102XX-1S10 XE | Passed     | Passed    |

There were not any appearance changes (such as melting, crazing or blistering) on the bodies. The discoloration levels by each sample were very slight. The changes of the wiper gaps (distance between opposite contacts on mating side) were slight.

5.4 Electrical

**Dielectric Withstanding Voltage — MIL-STD-202F Method 301**

*Purpose*

The purpose of this test is to prove that a given electrical connector can operate safely at its rated voltage and withstand momentary overpotentials due to switching, surges, and other similar phenomena.

*Test Method*

Withstanding voltage shall be tested in accordance with MIL-STD-202F Method 301.

|                  |                                    |
|------------------|------------------------------------|
| Applied Voltage: | 500 VAC <sub>RMS</sub> @ Sea Level |
| Duration:        | 1 minute                           |
| Observation:     | No evidence of a breakdown         |

*Test Results*

|                    |
|--------------------|
| All samples passed |
|--------------------|

**Insulation Resistance — MIL-STD-202F Method 302**

*Purpose*

The purpose of this test is to establish the methods and procedures to be followed in determining the resistance offered by the insulation materials and the various seals of a connector to a direct current potential tending to produce a leakage of current through or on the surface of these members.

*Test Method*

Insulation resistance shall be tested in accordance with MIL-STD-202F Method 302, Test Condition B.

|                  |                     |
|------------------|---------------------|
| Applied Voltage: | 500 V <sub>DC</sub> |
| Duration:        | 1 minute            |

*Test Results*

|               | Resistance        |
|---------------|-------------------|
| Between pins: | 10,000 MΩ Minimum |

## Important Notice

The information we are furnishing you is being provided free of charge and is based on tests performed at 3M laboratory facilities. While we believe that these test results are reliable, their accuracy or completeness is not guaranteed. Your results may vary due to differences in test types and conditions. This information is intended for use by persons with the knowledge and technical skills to analyze, handle and use such information. You must evaluate and determine whether the product is suitable for your intended application. The foregoing information is provided "AS-IS". In providing this information 3M makes no warranties regarding product use or performance, including any implied warranty of merchantability or fitness for a particular use.