



This is the refreshed model, updated with 48V external battery. Extra runtime is available by connecting up to four optional extended battery modules <u>BP48VRM2U</u> (sold separately).

SmartPro 1440VA 1440W 120V Line-Interactive Sine Wave UPS - 8 Outlets, Extended Run, Network Card Included, LCD, USB, DB9, 2U Rack/Tower

MODEL NUMBER: SMART1500RMXLN











Provides complete battery backup and pure sine wave power output for servers, switches and other highend distributed IT equipment.

Features

1.44kVA/1.44kW/120V Battery Backup for Distributed IT, Telecom or Enterprise Deployments
This rack-mount line-interactive UPS system provides reliable battery backup and AC power protection
against blackouts, brownouts, surges and line noise that can damage your valuable IT equipment or
destroy data. The SMART1500RMXLN is ideal power management for high-end in-rack networking
equipment, including servers, VoIP phones, data storage and PoE switches. Unity power factor ensures
the most watts possible at each power rating, so you can connect more equipment.

Reliable, Expandable Battery Backup Keeps You Operational Through Power Outages

The field-replaceable, hot-swappable VRLA battery modules allow you to work through short power failures and give you enough time to safely save files and shut down your system in case of a prolonged blackout. Switchover from line to battery power happens within milliseconds to maintain continuous operation of connected equipment without interruption or rebooting. Extra runtime is available by connecting up to four optional extended battery modules (BP48VRM2U, sold separately).

Pre-Installed LX Platform Network Management Card Allows Remote Access 24/7

The WEBCARDLXE network interface enables full remote configuration and management, including load shedding, reboots of connected equipment and safe shutdowns. The IP-based Auto Probe feature ensures continuous network uptime by communicating with other network devices, detecting lost connectivity and automatically rebooting IT equipment. Optional EnviroSense2 modules (E2MT, E2MTDO and E2MTHDI, all sold separately) provide a variety of environmental monitoring and control options.

NEMA 5-15R Outlets Protect Your Connected Components

Eight managed 5-15R outlets provide connected equipment with pure sine wave AC output and allow you to monitor power consumption down to the outlet group level. Power provided by these outlets is filtered to protect connected equipment against damaging surges and line noise. Four outlets are grouped into two programmable load banks that let you shed non-critical loads to extend runtime for critical loads. Front and rear cooling fans help protect equipment from overheating.

Automatic Voltage Regulation (AVR) Corrects Low- and High-Voltage Conditions

Highlights

- Protects equipment against blackouts, brownouts, transient surges and line noise
- Keeps equipment running during outages to allow time for file saves and safe shutdown
- Unity power factor ensures maximum power possible at each power rating
- ENERGY STAR 2.0-certified to save electricity, lower costs and protect the environment
- 2-line front-panel LCD with 10 selectable screens reports detailed UPS and site power info

Package Includes

- 1440VA 1440W 120V Line-Interactive UPS
- WEBCARDLXE network management card
- USB cable
- DB9 cable
- Rack-mounting hardware
- Tower support stands
- Safety instructions
- Quick Start Guide





AVR protects your equipment from incremental hardware damage, data loss and performance problems caused by brownouts. The SMART1500RMXLN maintains regulated 120V nominal output during brownouts and overvoltages from 80V to 151V while keeping the battery fully charged and ready to take over in case of power failure.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This UPS system filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

ENERGY STAR-Certified to Help You Save Money and Protect the Environment

By meeting strict U.S. Department of Energy and U.S. Environmental Protection Agency requirements, this ENERGY STAR 2.0 UPS system provides high operational efficiency to signal a reduction in BTU emissions, save on utility and cooling costs and help protect the environment.

Intuitive Front-Panel Interface for Convenient UPS Operation and Monitoring

The two-line front-panel LCD monitoring screen features 10 selectable screens that allow quick access to a wide range of detailed UPS and site power information. LEDs show UPS status: a green light means utility power is on, an orange light means the UPS is in battery mode and a red light indicates an active alarm or fault. The control panel rotates to accommodate both rack-mount and tower configurations.

Advanced Communications Ports Allow for Automatic Saves and Shutdowns

RS-232 and USB ports connect to a device for a variety of communication options (cables are included). A dry-contact relay port can be programmed through the LCD to provide reliable communications to automation and industrial components. The RPO/ROO port permits emergency shutdown or remote restart of all connected equipment.

Versatile Installation Options

You can mount the SMART1500RMXLN in just 2U of space in an EIA-standard 19-inch rack using the included hardware. You can also adapt it for tower installation using the included support stands. The 10-foot power cord with NEMA 5-15P plug connects to a compatible AC outlet.

Specifications

OVERVIEW			
UPC Code	037332178022		
UPS Type	Line-Interactive		
INPUT			
Input Phase	Single-Phase		
Rated input current (Maximum Load)	12A (120V)		
Nominal Input Voltage(s) Supported	120V AC		
UPS Input Connection Type	5-15P		
Input Circuit Breakers	80V-151V; adjustable to 70-153V		
UPS Input Cord Length (ft.)	10		
UPS Input Cord Length (m)	3.1		
Recommended Electrical Service	15A 120V		
Maximum Input Amps	12		





OUTPUT		
Output Capacity (VA)	1440	
Output Capacity (kVA)	1.44	
Output Capacity (Watts)	1440	
Output Capacity (kW)	1.44	
Power Factor	1	
Nominal Voltage Details	120v nominal output in battery mode	
Frequency Compatibility	50 / 60 Hz	
Output Voltage Regulation (Line Mode)	120V (-13%, +15%)	
Output Voltage Regulation (Battery Mode)	-10%, +6%	
Load Management Receptacles	Two switchable two-outlet 5-15R load banks	
Output AC Waveform (AC Mode)	Sine wave	
Output AC Waveform (Battery Mode)	Pure Sine wave	
Nominal Output Voltage(s) Supported	110V; 115V; 120V	
Output Receptacles	(8) 5-15R	
Individually Controllable Load Banks	Yes	
BATTERY		
Battery Type	Valve Regulated Lead Acid (VRLA)	
Runtime Full Load (min.)	5.1 min. (1440w)	
Runtime Half Load (min.)	15.1 min. (720w)	
Expandable Runtime	Yes	
Expandable Battery Runtime	Extended runtime supported via optional 48V DC BP48VRM2U external battery packs only.	
External Battery Pack Compatibility	BP48VRM2U (limit 4)	
DC System Voltage (VDC)	48	
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90% (typical, full load discharge)	
Battery Access	Front panel battery access door	
Internal UPS Replacement Battery Cartridge	Pre-August 2023: RBC93-2U">RBC93-2U - Post-August 2023: 744-A4801 -	
Battery Replacement Description	Hot-swappable, user replaceable 48V internal battery cartridge	
VOLTAGE REGULATION		





Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 80 to 151V (Normal Mode) or 70-153V (Extended Mode)		
Overvoltage Correction	Reduces incoming voltage between 132-151V by 13% (Normal Mode); 138-152V (Extended mode)		
Undervoltage Correction	Boost incoming voltages between 81-102V by 15% (Normal Mode); 71-92V by 15% (Extended Mode)		
USER INTERFACE, ALERTS & CON	USER INTERFACE, ALERTS & CONTROLS		
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)		
Switches	5 pushbutton switches control OFF / ON power status, ENTER, UP, and DOWN selection and ESC control functions. LX Platform Interface: Recessed reset switch for interface reboot and factory reset		
Alarm Cancel Operation	Press the ESC (Escape) button on the front panel display to silence the alarm. Check the alarm condition and perform the applicable action to resolve the condition. If the alarm status changes, the alarm beeps again, overriding the previous alarm silencing		
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions		
LED Indicators	3 status-indicating LEDs (normal, battery mode, alarm/fault); LED colors (green = ON, orange = On battery, flashing orange = below warning level, red = alarm/fault). LX Platform Interface Status: Network Link/Activity (Green): Flashes for network activity. Network Speed (Yellow): 10 Mbps (Flashing), 100 Mbps (On steady). Normal Operation (Solid Green); Software Update (Alternating Green/Orange ~1/sec); Factory Reset (Alternating Green/Orange ~2/sec).		
SURGE / NOISE SUPPRESSION			
EMI / RFI AC Noise Suppression	Yes		
AC Suppression Joule Rating	380		
AC Suppression Response Time	Instantaneous		
PHYSICAL			
Primary Form Factor	Rackmount; Tower		
Rack Height	2U		
Cooling Method	Fan		
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount; Tower		
Installation Form Factors Supported with Optional Accessories	4 post rackmount short-depth (4POSTRAILKITWM)		
Minimum Required Rack Depth (cm)	50.80		
Minimum Required Rack Depth (inches)	20		
Minimum Required Rack Depth with External Battery Pack (cm)	51		
Minimum Required Rack Depth with External Battery Pack (in.)	20		
Minimum Required Rack Depth without External Battery Pack (cm)	51		
Minimum Required Rack Depth without External Battery Pack (in.)	20		





Optional Mounting Accessory Notes	Optional 4POSTRAILKITWM enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm)
Primary UPS Depth (mm)	447
Primary UPS Height (mm)	88
Primary UPS Width (mm)	447
Shipping Dimensions (hwd / in.)	9.45 x 19.60 x 23.03
Shipping Dimensions (hwd / cm)	24.00 x 49.80 x 58.50
Shipping Weight (lbs.)	61.73
Shipping Weight (kg)	28.00
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	8.76 x 44.70 x 44.70
UPS Power Module Dimensions (hwd, in.)	3.45 x 17.6 x 17.6
UPS Power Module Weight (kg)	23.00
UPS Power Module Weight (lbs.)	50.71
Unit Dimensions (hwd / in.)	3.450 x 17.200 x 17.600
Unit Weight (lbs.)	50.706
Unit Weight (kg)	23.00
Mounting Details	Included 4-post mounting kit enables installation in 4 post racks. Two ABS mounting stands enables the UPS to be configured in an upright tower orientation.
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to +50°C)
Relative Humidity	0-95% non-condensing
AC Mode BTU / Hr. (Full Load)	83
AC Mode Efficiency Rating (100% Load)	96%
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	504
Operating Elevation	0-10000 ft. (0-3000 m)
Storage Elevation (ft.)	0-32,808
Audible Noise	45 dBA maximum, front side 1m
Storage Elevation (m)	0-10,000
COMMUNICATIONS	
Network Management Cards	WEBCARDLXE >
Network Monitoring Port Description	Pre-installed WEBCARDLXE supports detailed monitoring and management of UPS and site power conditions. Not





PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at https://tripplite.eaton.com/products/power-alert
Communications Cable	Micro-USB, USB and DB9 cabling included
Network Monitoring Port	RJ45 Network port, Micro-USB Configuration/Console port, USB A port supports a variety of Envirosense2 environmental and control modules. See Accessories>Management Hardware section for more information about these modules.
EPO Port	RJ11 interface jack with 4-meter cable included. Supports normally open and normally closed EPO systems
SNMP Compatibility	SNMP V1, V2c, V3
Network UPS Tools (NUT) Compatibility	NUT compatible. See a full list of NUT compatible Tripp Lite UPS systems at https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite
Network Management Card Description	Network management card included
Communications Interface	Contact closure; DB9 Serial; EPO (emergency power off); Micro-USB; Pre-installed network card; USB (HID enabled); USB-A
Emergency Power Off (EPO)/Remote On-Off (ROO)	Yes
LINE / BATTERY TRANSFER	
Transfer Time	1-4ms for normal mode, >5ms for sensitive mode
Low Voltage Transfer to Battery Power (Setpoint)	80 (adjustable to 70V)
High Voltage Transfer to Battery Power (Setpoint)	151
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (included); Automatic Voltage Regulation (AVR); Expandable battery backup; Hot swappable batteries; Remote management; Sine wave output; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
Grounding Details	Rear panel grounding lug
APPLICATIONS	
UPS Applications	Large Network; High-End Desktop/Small Network
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	RoHS; FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.