SPECIFICATIONS:						
NUMBER OF PHASES: 2	ROTOR INERTIA: 260 g-cm ² (1.42 oz-in ²) NOM					
STEPS PER REVOLUTION: 200	INSULATION CLASS: B					
STEP ANGLE: 1.8°	TEMP. RISE: 80 °C MAX.					
STEP TO STEP ACCURACY: ±0.09 1, 2	OPERATING TEMP. RANGE: -20 TO +50°C 9					
POSITIONAL ACCURACY: ±5% 1,3	STORAGE TEMP. RANGE: -30 TO+70 °C					
AXIAL MOVEMENT: 0.1mm MAX (100N AXIAL FORCE)	RELATIVE HUMIDITY RANGE: 15 TO 85 %					
BEARING SIZE: 28*15*7 mm	WEIGHT: 0.6 kg (1.32 lb)					
SHAFT MATERIAL: SUS303						

		7	8		1	1
	SPECIFICATION		INDUCTANCE	RATED	HOLDING	HOLDING
	CONNECTION	PER PHASE (ohm ±10%)	PER PHASE (mH ±20%)	CURRENT (amp)	TORQUE (Nm MIN)	TORQUE (oz—in Min)
BI-POLAR SERIES		1.6	6.9	2.2	1.5	212.4

REVISIONS						
ECO NO.	REV	DATE	APPROVED			
7068	Α	PRELIMINARY RELEASE	10/24/14	D.MACLEOD		
7445	В	REVISE NOTE 11	6/6/16	J.KORDIK		
8359	С	1ST ANGLE TO 3RD	10/31/19	J.KORDIK		
		_	_	-		
-	_	_	_	_		
		_	_	_		
		_	_	-		
-	_	_	_	_		
_	_	_	_	_		
_	_	_	_	_		

0

HH2.


NOTES, UNLESS OTHERWISE SPECIFIED:

- 1 MEASURMENTS MADE AT RATED CURRENT IN EACH PHASE.
- 2 BETWEEN ANY TWO ADJACENT FULL STEP POSITIONS.
- MAXIMUM ERROR IN 360°.
- 4 HIPOT 500 VAC, 60 Hz FOR ONE MINUTE.
- 5 CONNECTOR: JSTS6B-XH-A-1(LF)(SN)
- 6 INSULATION RESISTANCE: 100 MEGOHMS MIN AT 500 VDC.
- 7 AS MEASURED ACROSS EACH PHASE.
- 8 AS MEASURED ACROSS EACH PHASE USING AN A.C. INDUCTANCE BRIDGE AT 1 KHz.
- 9 AS MEASURED BY THE CHANGE IN RESISTANCE METHOD, WITH RATED

CURRENT APPLIED TO 2 PHASES; WITH MOTOR AT REST.


- 10 ROTOR & STATOR LAMINATED CONSTRUCTION.
- 11 THIS MOTOR IS MANUFACTURED IN COMPLIANCE WITH THE CURRENT EU RoHS DIRECTIVE.
- 12 MOTOR LABEL TO INCLUDE "ROHS" COMPLIANT, AMP P/N, 'MADE IN (COUNTRY OF ORIGIN)', AND DATE CODE.
- 13 HIGH TORQUE MOTOR DESIGN.

LABEL DETAIL




FULL STEP SWITCHING SEQUENCE BI-POLAR. FACING MOUNTING END

			. , , , , , , , , , , , , , , , , , , ,			
	STEP	A+	A-	B+	B-]CCW
	0	+	_	+	_	≱
	1	1	+	+	1	
	2		+		+	
1	3	+		1	+	
CW	4	+		+	_	



CONTRACT NO.	APPLIED MOTION PRODUCTS, INC.						
APPROVALS	DATE						
DRAWN K.KESLER	10/31/19	STEP MOTOR OUTLINE					
CHECKED R.JONEZ	10/31/19		COMPI	JTER DATA	DWG NO.		REV
APPROVED J.KORDIK	10/31/19	B		DRAWING	D#G NO.	HH23-101	C
APPROVED		SCALE:	NONE			SHEET 1 OF 2	



*ALL DIMENSIONS IN MM

DECIMALS: MM $X.XX = \pm 0.13$ $X.X = \pm 0.25$ $X = \pm 0.5$

COMPUTER DATA

BASE DRAWING

ANGLES: MACH. = $\pm 0.5^{\circ}$ CHAM. = $\pm 5^{\circ}$ **APPROVALS**

K.KESLER

CHECKED R.JONEZ

APPROVED

DATE

10/31/19

10/31/19

В

SCALE: NONE

DWG NO.

STEP MOTOR OUTLINE

HH23-101

SHEET 2 OF 2

REV

С