

SPECIFICATIONS:	
STEPS PER REVOLUTION: 200	ROTOR INERTIA: 1850 G-CM ² (10.1 OZ-IN ²) NOM
STEP ANGLE: 1.8°	DETENT TORQUE: 2550 G-CM (35.4 OZ-IN) MIN
STEP TO STEP ACCURACY: ±.09 DEGREES [1], [2]	INSULATION CLASS: B
POSITIONAL ACCURACY: ±.09 DEGREES [1], [3]	BEARINGS: ABEC 3, DOUBLE SHIELDED
HYSTERESIS: - %	WEIGHT: 2.95 KG (6.5 LB)
SHAFT RUNOUT: 0.05 T.I.R.	TEMP. RISE: 80 °C MAX. [8]
RADIAL PLAY: 0.02 MAX W/A .5KG RADIAL LOAD	OPERATING TEMP. RANGE: -20 TO +50 °C
END PLAY: 0.08 MAX W/A .5KG AXIAL LOAD	STORAGE TEMP. RANGE: -30 TO +70 °C
	RELATIVE HUMIDITY RANGE: 15 TO 85 %

[7]						
SPECIFICATION CONNECTION	NUMBER OF PHASE	RESISTANCE PER PHASE OHM ±10%	INDUCTANCE PER PHASE mH ±20%	RATED CURRENT Amp	HOLDING TORQUE Nm Min	HOLDING TORQUE oz-in min
BI-POLAR SERIES	2	1.32	10.8	3.18	6.0	849.7
BI-POLAR PARALLEL	2	0.33	2.7	6.3	6.0	849.7
UNI-POLAR	4	0.66	2.7	4.5	4.3	637.2

NOTES, UNLESS OTHERWISE SPECIFIED:


- [1] MEASUREMENTS MADE AT RATED CURRENT IN EACH PHASE.
- [2] BETWEEN ANY TWO ADJACENT STEP POSITIONS.
- [3] MAXIMUM ERROR IN 360°.
- 4. HIPOT 500 VAC, 60 Hz FOR ONE MINUTE.
- [5] LEADS: 8, 22AWG, 7 STRAND MIN.,UL AND CSA APPROVED, UL 1430 OR UL 3265, 3266.
- 6. INSULATION RESISTANCE: 100 MEGOHMS MIN AT 500 VDC.
- [7] AS MEASURED USING AN A.C. INDUCTANCE BRIDGE, AT 1KHz.
- [8] AS MEASURED BY THE CHANGE IN RESISTANCE METHOD, WITH RATED VOLTAGE APPLIED TO 2 PHASES; WITH MOTOR AT REST.
- [9] SHAFT OPTION: IF DOUBLE SHAFT REQUIRED ADD "D" TO END OF PART NUMBER. DOUBLE SHAFT REQUIRES ADDED HOLES FOR ENCODER OPTIONS.
- 10. THIS MOTOR IS MANUFACTURED IN COMPLIANCE WITH THE CURRENT EU RoHS DIRECTIVE.
- [1] MOTOR LABEL TO INCLUDE "ROHS" COMPLIANT, 'MADE IN (COUNTRY OF ORIGIN)' AND DATE CODE.
- 10. HIGH TORQUE MOTOR DESIGN.

BIPOLAR, FULL STEP, 2 PHASE ON
PARALLEL CONNECTED

SWITCHING SEQUENCE FOR CW ROTATION
 FACING MOUNTING END

STEP	ORANGE & BLK/WHT	BLACK & ORN/WHT	RED & YEL/WHT	YELLOW & RED/WHT
0	+	-	+	-
1	-	+	+	-
2	-	+	-	+
3	+	-	-	+
4	+	-	+	-

↑
CCW



REVISIONS				
ECO NO.	REV	DESCRIPTION	DATE	APPROVED
5982	A	INITIAL RELEASE	10/5/09	J KORDIK
6030	B	SPECS CHANGED	12/2/09	J KORDIK
7247	C	ADD UL TO LABEL	1/26/16	J KORDIK
7447	D	REVISE NOTE 10	1/26/16	J KORDIK
7606	E	ADD HOLE PATTERN	3/30/17	J KORDIK
8209	F	DOCUMENT CLEANUP	4/29/19	J KORDIK
8383	G	REVISE WEIGHT	12/10/19	M.COX

HT34-505

HT34-505 XX-XX
 PARALLEL - 6.3A/0.33 OHM
 RoHS MADE IN X

www.applied-motion.com




LABEL DETAIL
BOTH OPTIONS ACCEPTABLE


HT34-505 XX-XX
 SERIES - 3.18A/1.32 OHM
 PARALLEL - 6.3A/0.33 OHM
 HOLD. TORQUE - 6.0 N.m
 RoHS MADE IN X

www.applied-motion.com

[11]

CONTRACT NO. -				
APPROVALS		STEP MOTOR OUTLINE		
DRAWN	DATE			
<i>R.JONEZ</i>	8/31/09			
CHECKED				
APPROVED				
APPROVED				
SCALE: NONE		COMPUTER DATA BASE DRAWING	DWG NO. HT34-505	REV G
		SHEET 1 OF 2		



TOLERANCES		THIRD ANGLE PROJECTION		 APPLIED MOTION PRODUCTS, INC.					
DECIMALS: MM (INCH) X.XXX = ±0.013 (.005) X.XX = ±0.25 (.01) X.X = ±2.5 (0.1) ANGLES: MACH. = ±5° CHAM. = ±5°									
COMPUTER DATA BASE DRAWING		APPROVALS		DATE		STEP MOTOR OUTLINE			
		DRAWN R. JONEZ		8/28/09					
		CHECKED				B	DWG NO. HT34-505		REV G
		APPROVED				SCALE: NONE		SHEET 2 OF 2	