

AANI-AP-0200

Request Samples



Check Inventory



18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A


Features


- Full-Constellation Active GNSS Antenna
- Low Profile with Size 18 x 18 x 6.6 mm
- LNA Gain: 15 ± 3 dB
- Pre-Filtering for Enhanced Anti-Jamming Performance
- Low Current Consumption: 5 ± 3 mA
- Custom Cable & Connector Options Available

Applications

- Asset Tracking
- Fleet Management
- Micro-Mobility Solutions
- UAVs, Robotics & Autonomous Vehicles
- Precision GNSS Positioning
- Mission-Critical GNSS Timing
- Geofencing

Product Image





AANI-AP-0200

Request Samples




Check Inventory




18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A

GNSS Frequency Bands Covered

	L1 1575.42MHz	L2 1227.6MHz	L5 1176.45MHz	
GPS	■	□	□	
GLONASS	G1 1598.06-1609.31MHz	G2 1242.93-1251.68MHz	G3 1202.025MHz	
	■	□	□	
Galileo	E1 1575.42MHz	E5a 1176.45MHz	E5b 1201.5MHz	E6 1278.75MHz
	■	□	□	□
BeiDou	B1 1561MHz	B2 1207.14MHz	B3 1268.52MHz	
	□	□	□	
QZSS	L1 1575.42MHz	L2 1227.6MHz	L5 1176.45MHz	L6 1278.75MHz
	■	□	□	□
IRNSS/NAVIC			L5 1176.45MHz	
			□	
SBAS	L1/E1/B1 1575.42MHz		L5/B2a/E5a 1176.45MHz	
	■		□	



Frequency allocation: GNSS systems, upper L bands and lower L bands

**AANI-AP-0200**

Request Samples




Check Inventory


18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A

Electrical Specification

Parameters		Min.	Typ.	Max.	Units	Note
Antenna						
Frequency		GPS: L1 GLONASS: G1 GALILEO: E1 QZSS: L1 SBAS: L1				
VSWR		≤ 2			-	
Polarization		RHCP			-	(Right Hand Circular Polarization)
Nominal Impedance		50			Ω	
Peak Gain (RHCP)		0.16	0.8	2.1	dBic	On 70 × 70 mm ground plane
Efficiency		58.3	58.9	78.1	%	
LNA						
VSWR		≤ 2.0			-	
DC Input		1.8		5.0	V	
Gain		15 ± 3			dB	
Noise Figure		≤ 2.6			dB	
Out of Band Attenuation	10-840 MHz	> 50			dB	
	840-1500 MHz	> 60				
	1700-2000 MHz	> 50				
	2000-3000 MHz	> 50				
Current Consumption		5 ± 3			mA	

Please note: All measurement data is based on the standard configuration (conducted in free space unless otherwise specified).

**AANI-AP-0200**

Request Samples



Check Inventory

**18 x 18 x 6.6 mm**
RoHS Compliant
MSL Level = N/A

Mechanical Specification


Parameter	Specification
Antenna Dimension	18 x 18 x 6.6 mm
Mounting Type	Adhesive Mount
RF Connector ⁽¹⁾	u.FL/IPEX-1/MHF1
Cable Length ⁽¹⁾	Ø 1.13mm x 100 mm

(1): Fully customizable RF Cable & Connector

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +85°C
RoHS Compliance	Yes
ESD Sensitive	No
Relative Humidity	Up to 95%

Full-Constellation Internal Active GNSS L1 Patch Antenna



AANI-AP-0200

Request Samples



Check Inventory



18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A

Ordering Information

Part Number	Description	Connector Option
AANI-AP-0200-1	Full-Constellation Internal Active GNSS L1 Patch Antenna with 100 mm cable & MHF1connector	u.FL/IPEX-1/MHF1
AANI-AP-0200-2	Full-Constellation Internal Active GNSS L1 Patch Antenna with 150 mm cable & MHF1connector	u.FL/IPEX-1/MHF1
AANI-AP-0200-3	Full-Constellation Internal Active GNSS L1 Patch Antenna with 60 mm cable & MHF1connector	u.FL/IPEX-1/MHF1

Note: Different cable and connector configurations that are not listed may be available upon request via [Abracon online support](#)




12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 09-02-25

ABRACON IS
ISO9001-2015
CERTIFIED

Full-Constellation Internal Active GNSS L1 Patch Antenna



AANI-AP-0200

Request Samples




Check Inventory




18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A

Product Dimension



PART NUMBER	CABLE LENGTH (L)	CONNECTOR
AANI-AP-0200-1	100	U.FL/IPEX-1/MHF1
AANI-AP-0200-2	150	U.FL/IPEX-1/MHF1
AANI-AP-0200-3	60	U.FL/IPEX-1/MHF1

Unit: mm



AANI-AP-0200

Request Samples




Check Inventory





18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A

Measurement Setup



GNSS Block Diagram





AANI-AP-0200

Request Samples






Check Inventory



18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A

Reflection Characteristics – Return Loss & VSWR





AANI-AP-0200

Request Samples





Check Inventory



18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A

Radiation Characteristics –Passive Peak Gain





AANI-AP-0200

Request Samples





Check Inventory



18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A

Radiation Characteristics –Passive Efficiency





AANI-AP-0200

Request Samples





Check Inventory



18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A

LNA Characteristics –LNA Gain





AANI-AP-0200

Request Samples






Check Inventory




18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A

Radiation Characteristics – 3D & 2D Pattern


1561MHz




XY plane




XZ plane



YZ plane



Full-Constellation Internal Active GNSS L1 Patch Antenna



AANI-AP-0200

Request Samples





Check Inventory




18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A


1575MHz




XY plane



XZ plane



YZ plane




12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 09-02-25

ABRACON IS
ISO9001-2015
CERTIFIED

Full-Constellation Internal Active GNSS L1 Patch Antenna



AANI-AP-0200

Request Samples






Check Inventory




18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A


1602MHz




XY plane



XZ plane




YZ plane



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 09-02-25

ABRACON IS
ISO9001-2015
CERTIFIED



AANI-AP-0200

Request Samples



Check Inventory



18 x 18 x 6.6 mm
RoHS Compliant
MSL Level = N/A

Packaging

AANI-AP-0200-1:

600 pcs antennas per carton

Dimensions: 345 x 210 x 360 mm

AANI-AP-0200-2:

400 pcs antennas per carton

Dimensions: 345 x 210 x 360 mm

AANI-AP-0200-3:

600 pcs antennas per carton

Dimensions: 345 x 210 x 360 mm

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf ('COTS'), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 09-02-25

ABRACON IS
ISO9001-2015
CERTIFIED