



GC Series



HIW



DR



Switching Operation	Slow Action	Snap Action	Slow Action	Snap Action
1 NC / 1 NO Contacts	602.1120.057 GC-U1Z HIW 	602.1370.629 GC-SU1Z HIW 	-	602.1191.099 GC-SU1Z DR
2 NC Contacts	602.1820.175 GC-A2Z HIW 	-	-	-
2 NO Contacts	602.1820.157 GC-E2 HIW 	-	-	-
1 NC / 1 NO Contacts Overlapping	602.1320.058 GC-UV1Z HIW 	-	-	-
Replacement actuator:	391.2200.552		391.2410.593	

Technical Information

	Slow Action	Snap Action	Slow Action	Snap Action
Maximum Switching Voltage	240V	240V	240V	240V
Max. Switching Amps (up to)*	10A	10A	10A	10A
B10d (up to)*	20 Million	20 Million	20 Million	20 Million
Mechanical Service Life (up to)*	3 x 10 ⁶	10 x 10 ⁶	10 x 10 ⁶	10 x 10 ⁶
Switching Frequency	≤ 100/min	≤ 100/min	≤ 100/min	≤ 100/min
Operating Temperature	-30 °C to +80 °C	-30 °C to +80 °C	-30 °C to +80 °C	-30 °C to +80 °C
Protection Rating	IP65	IP65	IP65	IP65
Utilization Category (up to)*	AC-15, Ue/Ue 240V 3A	AC-15, Ue/Ue 240V 3A	AC-15, Ue/Ue 240V 3A	AC-15, Ue/Ue 240V 3A
Rate Insulation Voltage	400VAC	400VAC	400VAC	400VAC

Approvals

* Depending on switching system - see technical information for details



Special features/variants (on request)

- Available with different actuator directions, steel roller and additional contacts:
- 2 NC / 1 NO overlapping contact (larger enclosure)
- 2 NC / 2 NO contact (larger enclosure)

Drawing dimensions in mm