



[Article Page](#)

Product Description



inductive sensor DC



Name
Order number
Switching distance
Mounting


Switch type

Signal Type
Connection
Connection diagramm

KJ2-Q8AB-DPS-V1-AM
08310000369
2 mm

 shielded

 N.O.
DC PNP
connector M8



Q 8 x 8 x 42

Dimension (in mm)
Technical Specification
Operating voltage
Max. ripple
Voltage drop
Max. load current
No load current
Leakage current
Switching frequency
Switching hysteresis
Operating temperature
Temperature drift
Repeat accuracy
Switching state
Time delay
Short-circuit proof
Overload protection
Reverse voltage protection
Protection category
EMC-level
Housing material
Material active face
Utilisation category

10 - 30 VDC
 $\leq 10 \%$
2,4 V
200 mA
 $\leq 13 \text{ mA}$
 $\leq 10 \mu\text{A}$
1000 Hz
 $\leq 15 \%$
-25 ° C to 70 ° C
 $\leq 10 \%$
 $\leq 5 \%$
LED
100 ms
yes
yes
yes
IP67
DIN EN 60947-5-2: 2008
Aluminum
Ultramid schwarz
DC13



KJ2-Q8AB-DPS-V1-AM

Pulsotronic GmbH & Co. KG Neue Schichtstraße 14b 09366 Niederdorf Deutschland +49 (0)37296 930-200

Contact material
Contact surface material
Termination
FIT / MTTF acc. to SIEMENS 29500

Cu
NiAu
Connector M8 3pin
58,05 / 1966y

Errors and omissions excepted