

Technical Datasheet

HI-CONTACT™ 4-PASS COLD PLATE



HI-CONTACT™ LIQUID COLD PLATE

Boyd Hi-Contact™ tube liquid cold plates feature a high performance assembly utilizing a continuous tube press fit into an extruded aluminum plate. The patented geometry used in the Boyd Hi-Contact™ process moves the fluid closer to the device generating heat, achieving the best thermal performance from a tube cold plate.

To further increase the performance of Boyd's Hi-Contact™ liquid cold plates, a thermal epoxy is applied to the joint to provide a gap free thermal interface between the tube and the plate.

AVAILABLE OPTIONS

- Custom Sizes Available – See Boyd Custom Hi-Contact Cold Plates for Design Guidelines
- Tube Material: Stainless Steel, Cupronickel
- Finishes: AavSHIELD, AavSHIELD³

PART NUMBERS

416501U00000G – Unfinished, Standard 152mm Plate Length

416601U00000G – Unfinished, Standard 305mm Plate Length

HI-CONTACT™ PRODUCT SPECIFICATIONS

Property	Details
Plate Details	Extruded Aluminum
Tube Material	Copper
	9.5mm O.D. x 1.24mm wall
Standard Finish	Unfinished
Epoxy	Aluminum Filled - High Thermal Conductivity

Measurement	mm	in
Width	127	5
Thickness	15.24	0.55



FEATURES & BENEFITS:

- Cost Effective
- High Performance Leak Free Joints
- Hi-Contact™ for Better Heat Transfer
- Easy to Customize

NOTICE: The information included in this data sheet is believed to be accurate and reliable. BOYD assumes no responsibility for end use applications and no performance warranty is expressed or implied.

Technical Datasheet


HI-CONTACT™ 4-PASS COLD PLATE

BOYD
TRUSTED INNOVATION

MECHANICAL


Dimensions are shown in mm

Figure 1



PERFORMANCE – 4 PASS

Figure 2



NOTICE: The information included in this data sheet is believed to be accurate and reliable. BOYD assumes no responsibility for end use applications and no performance warranty is expressed or implied.