


MINI MOLDED POWER INDUCTOR



AOTA-B252010S

Request Samples



Check Inventory



2.5 x 2.0 x 1.0 mm
RoHS/RoHS II Compliant
MSL Level = 1

Features

- Shielded construction for minimized EMI emissions
- Low DCR for better efficiency
- High current handling capability
- Compact size that is suitable for high-density designs
- Fit for high-frequency switching applications due to high SRF

Applications

- Consumer electronics and portable devices
- Power electronics such as DC-DC converters, inverters and voltage regulators
- Industrial applications, robotics, signal conditioning, instrumentation and control systems
- IoT devices, smart home, automation systems and wireless sensing

Electrical Specifications

Part Number	Inductance	Tolerance	Self-Resonant Frequency	DC Resistance		Saturation Current		Temperature Rise Current	
	1MHz/1.0V		Min.	Typ	Max	Typ	Max	Typ	Max
Units	μH	%	MHz	mΩ		A		A	
Symbol	L	M	SRF	DCR		Isat		Irms	
AOTA-B252010SR33MT	0.33	20	95	13	16	8.5	7.5	5.5	5.0
AOTA-B252010SR47MT	0.47	20	81	16	20	7.0	6.5	6.1	5.7
AOTA-B252010SR68MT	0.68	20	63	24	29	6.6	5.8	5.2	4.5
AOTA-B252010S1R0MT	1.0	20	53	27	30	5.4	5.0	4.7	4.5
AOTA-B252010S1R5MT	1.5	20	35	37	42	4.0	3.7	4.1	3.6
AOTA-B252010S2R2MT	2.2	20	27	57	65	3.5	3.2	2.6	2.3
AOTA-B252010S3R3MT	3.3	20	22	95	110	2.9	2.6	2.2	1.9
AOTA-B252010S4R7MT	4.7	20	19	124	136	2.2	1.9	1.7	1.6
AOTA-B252010S100MT	10.0	20	14	360	420	1.7	1.5	1.4	1.2

Test Conditions

Isat: DC current at which the inductance drops 30% from its nominal value.

Irms: DC current that causes the temperature rise (ΔT , approximate 40 °C) from 25°C ambient.

Operating Temperature: -40°C ~ +125°C (including self-temperature rise)

Storage Condition: -40°C ~ +125°C (on board), -10°C ~ +40°C (with packaging) and R.H. 60 max.

Working Voltage: 20V

AOTA-B252010S Series is **RoHS Compliant and Pb free**.



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
7/23/2025

ABRACON IS
ISO9001-2015
CERTIFIED

MINI MOLDED POWER INDUCTOR



AOTA-B252010S

Request Samples




Check Inventory




2.5 x 2.0 x 1.0 mm
RoHS/RoHS II Compliant
MSL Level = 1

Performance Graphs



Part Identification

AOTA-B252010S



MINI MOLDED POWER INDUCTOR



AOTA-B252010S

Request Samples




Check Inventory




2.5 x 2.0 x 1.0 mm
RoHS/RoHS II Compliant
MSL Level = 1

Mechanical Specifications



Recommended Land Pattern (Typ.)



Dimensions: Inch[mm]

Marking

No Marking



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
7/23/2025

ABRACON IS
ISO9001-2015
CERTIFIED

MINI MOLDED POWER INDUCTOR



AOTA-B252010S

Request Samples




Check Inventory



2.5 x 2.0 x 1.0 mm
RoHS/RoHS II Compliant
MSL Level = 1

Reflow Profile



Zone	Description	Temperature	Times
1	Preheat	T _{SMIN} ~ T _{SMAX} 150°C ~ 200°C	60 ~ 120 sec.
2	Reflow	T _L 217°C	60 ~ 90 sec.
3	Peak heat	T _P 260°C Max	10 sec. MAX

MINI MOLDED POWER INDUCTOR



AOTA-B252010S

Request Samples




Check Inventory




2.5 x 2.0 x 1.0 mm
RoHS/RoHS II Compliant
MSL Level = 1

Packaging

Tape & Reel: 3000 pcs/reel



A	B	P	K	T
2.30 ± 0.1	2.80 ± 0.1	4.0 ± 0.1	1.30 Max	0.3 Max



Dimensions: mm

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf (COTS, which are designed, intended and validated for use in commercial, industrial and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



5101 Hidden Creek Ln, Spicewood TX 78669
 Phone: 512-371-6159 Fax: 512-351-8858
 For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
7/23/2025

ABRACON IS
 ISO9001-2015
 CERTIFIED