

AVR-1F140805S

Request Samples



Check Inventory



13.6 x 7.8 x 5.2 mm
RoHS/RoHS II Compliant
MSL Level = 1

Features

- Shielded construction
- Soft saturation
- High Power Density
- Low DCR, High Efficiency
- Perfect for multi-phased power circuitry

Applications

- Desktop/ Server applications
- High current point-of-load (POL) converters
- Lighting
- Solar inverters and power
- Industrial and robotics
- Medium and high-power switch mode power supplies.

Electrical Specifications

Part Number	Inductance	Tolerance	DC Resistance	Saturation Current (Typ)		Temperature Rise Current
	0.1MHz/1.0V			@25°C	@100°C	Min.
Units	nH	%	mΩ ±15%	A		A
Symbol	L		DCR	Isat		Irms
AVR-1F140805SR10K	100	±10%	0.17	76	61	58
AVR-1F140805SR22K	220	±10%	0.17	45	40	58

Test Conditions

Isat: DC current at which the inductance drops 30% from its value without current.

Irms: DC current that causes the temperature rise (ΔT , approximate 40 °C) from 20°C ambient


Operating Temperature: -40°C ~ +125°C (including self-temperature rise)

Storage Condition: -40°C ~ +85°C (with packaging) and R.H. <95% max

Operating Voltage: 40V (across inductor)

AVR-1F140805S Series is **RoHS Compliant and Pb free**

Part Identification





AVR-1F140805S

Request Samples




Check Inventory




13.6 x 7.8 x 5.2 mm
RoHS/RoHS II Compliant
MSL Level = 1

Mechanical Specifications




Dimensions: Inches [mm]

Recommended Land Pattern



Dimensions: Inches [mm]



AVR-1F140805S

Request Samples




Check Inventory




13.6 x 7.8 x 5.2 mm
RoHS/RoHS II Compliant
MSL Level = 1

Reflow Profile



Zone	Description	Temperature	Times
1	Preheat	$T_{SMIN} \sim T_{SMAX}$ 150°C ~ 200°C	60 ~ 120 sec.
2	Reflow	T_L 217°C	60 ~ 150 sec.
3	Peak heat	T_p 260°C	5 sec. MAX



AVR-1F140805S

Request Samples




Check Inventory



13.6 x 7.8 x 5.2 mm
RoHS/RoHS II Compliant
MSL Level = 1


Packaging

Tape & Reel: 800 pcs/reel



Series	W	E	F	P ₀	P ₁	P ₂	D ₀	A ₀	B ₀	T	K ₀
AVR-1F140805S	24.00 ± 0.30	1.75 ± 0.10	11.50 ± 0.10	4.0 ± 0.1	12.0 ± 0.1	2.0 ± 0.1	1.5 + 0.1/- 0.0	8.3 ± 0.10	14.3 ± 0.10	0.40 ± 0.05	5.30 ± 0.10

Dimensions: mm



ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf (COTS, which are designed, intended and validated for use in commercial, industrial and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION A : 7/7/2025

ABRACON IS
ISO9001-2015
CERTIFIED